



Page 67

206 TAPPING SCREWS
OVAL SLOT HEAD

BRIGHT PLATED 



Std. Package 100 Pcs.


Stock No.	Size	Each	Per 100
206-043	4 x 1/2	\$.05	\$2.75
206-085	6 x 3/8	.05	2.68
206-087	x 1/2	.05	2.93
206-088	x 5/8	.06	3.32
206-089	x 3/4	.06	3.61
206-091	x 1"	.10	5.97
206-093	x 1-1/4	.12	7.15
206-137	8 x 1/2	.06	3.43
206-138	x 5/8	.06	3.84
206-139	x 3/4	.07	4.43
206-141	x 1"	.08	4.82
206-143	x 1-1/4	.08	4.64
206-189	10 x 1/2	.07	4.14
206-190	x 5/8	.08	4.84
206-191	x 3/4	.09	5.38
206-192	x 7/8	.18	10.36
206-193	x 1"	.10	5.90
206-195	x 1-1/4	.14	8.52
206-248	12 x 3/4	.11	6.27
206-250	x 1"	.14	8.16
206-254	x 1-1/2	.18	10.40
206-278	14 x 3/4	.17	9.84
206-280	x 1"	.19	11.25


Ability to supply is subject to availability.

Page 69

208 TAPPING SCREWS
SOCKET

210

BRIGHT PLATED 



BRIGHT PLATED

Standard Package 100 Pieces

Stock No.	Size	Each	Per 100
208-039	4 x 1/4	\$.09	\$5.57
208-041	x 3/8	.06	3.34
208-043	x 1/2	.06	3.48
208-045	x 3/4	.06	3.79
208-047	x 1"	.08	5.00
208-083	6 x 1/4	.10	5.93
208-085	x 3/8	.06	3.57
208-087	x 1/2	.07	3.89
208-088	x 5/8	.07	3.93
208-089	x 3/4	.07	4.18
208-091	x 1"	.08	4.95
208-093	x 1-1/4	.10	6.04
208-095	x 1-1/2	.12	7.22
208-135	8 x 3/8	.07	4.04
208-137	x 1/2	.07	4.39
208-138	x 5/8	.08	4.66
208-139	x 3/4	.08	4.88
208-141	x 1"	.09	5.36
208-143	x 1-1/4	.11	6.65
208-145	x 1-1/2	.13	7.43
208-148	x 2"	.18	10.52
208-187	10 x 3/8	.08	4.95
208-189	x 1/2	.09	5.23
208-190	x 5/8	.09	5.34
208-191	x 3/4	.09	5.52
208-193	x 1"	.11	6.75
208-195	x 1-1/4	.14	8.02
208-197	x 1-1/2	.15	8.61
208-200	x 2"	.21	12.63

Page 69

208 TAPPING SCREWS
SOCKET (CONTINUED)


209

Stock No. Size Net

Pan Hd.	Flat Hd.	Truss Hd.	Each	Per 100
208-246	209-246	-	12 x 1/2	\$.12 \$7.22
208-248	209-248	-	x 3/4	.13 7.91
208-250	209-250	-	x 1"	.15 8.90
208-252	209-252	-	x 1-1/4	.17 9.83
208-254	209-254	-	x 1-1/2	.19 11.36
208-257	-	-	x 2"	.28 16.79
208-277	209-277	-	14 x 5/8	.17 10.08
208-278	209-278	-	x 3/4	.18 10.91
208-280	209-280	-	x 1"	.20 12.02
208-282	209-282	-	x 1-1/4	.25 14.95
208-284	209-284	-	x 1-1/2	.26 15.56
208-287	209-287	-	x 2"	.34 20.10

Page 69

213 HEXAGON HEAD
TAPPING SCREWS

BRIGHT PLATED 

Std. Package 100 Pcs.

Stock No.	Size	Each	Per 100
213-085	6 x 3/8	\$.11	\$6.73
213-137	8 x 1/2	.13	7.72
213-139	x 3/4	.17	9.93
213-141	x 1"	.19	10.99
213-143	x 1-1/4	.21	12.33
213-145	x 1-1/2	.23	13.47
213-187	10 x 3/8	.16	9.65
213-189	x 1/2	.17	10.27
213-190	x 5/8	.18	10.66
213-191	x 3/4	.19	11.43
213-193	x 1"	.24	14.29
213-246	12 x 1/2	.28	16.47
213-248	x 3/4	.30	17.56
213-250	x 1"	.33	19.58
213-276	14 x 1/2	.29	17.01
213-277	x 5/8	.27	16.18
213-278	x 3/4	.29	17.08
213-280	x 1"	.32	18.97
213-282	x 1-1/4	.33	19.79
213-284	x 1-1/2	.37	22.15
213-442	5/16 x 3/4	.68	40.32
213-444	x 1"	.79	46.84
213-446	x 1-1/4	.96	56.65
213-448	x 1-1/2	.99	58.75
213-489	3/8 x 1"	1.26	74.80
213-493	x 1-1/2	1.48	87.84

Page 69

222 'SPEE-DRILL' SCREWS
BRIGHT PLATED

BRIGHT PLATED 

Std Package 100 Pcs.

Stock No.	Size	Each	Per 100
222-085	6 x 3/8	\$.09	\$5.57
222-111	7 x 1/2	.10	6.18
222-137	8 x 1/2	.11	6.72
222-189	10 x 1/2	.14	8.43
222-191	10 x 3/4	.18	10.58

Standard Package 1000 Pieces

Stock No.	Size	Each	Per 1000
222-585	6 x 3/8	\$.08	\$47.54
222-611	7 x 1/2	.09	52.40
222-637	8 x 1/2	.10	60.17
222-689	10 x 1/2	.13	76.64
222-691	10 x 3/4	.16	96.04

Page 83

222 'SERT-A-NUTS'

Standard Package 25 Pieces


Stock No.	Size	Each	Each
222-304	6-32	\$.88	\$.52
222-306	8-32	1.02	.60
222-308	10-24	1.04	.62
222-310	1/4-20	1.41	.84

'SERT-A-NUT' KITS

Stock No.	Size	Each	Each
222-314	6-32	\$15.95	\$9.44
222-316	8-32	15.95	9.44
222-318	10-24	15.95	9.44
222-320	1/4-20	15.95	9.44

Page 72

222 MAGNETIC NUTSETTERS
CARDED



Individually Carded

Stock No.	Size	Per Card
222-355	1/4 x 3 Bit Holder	\$7.78
222-360	1/4 x 1-7/8	6.43
222-365	5/16 x 1-7/8	6.43
222-366	3/8 x 1-7/8	6.96
222-367	7/16 x 1-7/8	6.96
222-368	1/2 x 1-7/8	7.83
222-370	1/4 x 2-9/16	7.64
222-375	5/16 x 2-9/16	7.90
222-376	3/8 x 2-9/16	7.90
222-377	7/16 x 2-9/16	7.90
222-378	1/2 x 2-9/16	8.79

For Magnetic Nutsetter Kits see page 47.

Page 71

222 BIT ACCESSORIES



Individually Skin-Packed


Stock No.	Description	Each
222-380	Power Bit Belt w/9 assorted Bits	\$15.54
222-382	Screw Starter Driver w/3 Sq. Bits	13.08
222-384	Quick Change Chuck w/4 Bits	17.20
222-385	Drywall Screw Dimpler w/Bit	3.69
222-388	Ratchet Key	13.86

222 MAGNETIC SCREWDRIVER SET
CARDED

Stock No.	Each
222-996	Driver with 6 Bits \$23.74

Page 67

223 THREAD CUTTING SCREWS

BRIGHT PLATED 

Type 1

Stock No.	Size	Round (R)	Hexagon (H)
223-010	4-40 x 3/8	R	\$.22 \$13.04
223-014	6-32 x 3/8	PAN	.23 13.49
223-016	x 1/2	R	.25 14.93
223-022	x 3/4	R	.26 15.65
223-034	8-32 x 3/8	R	.28 16.65
223-037	x 1/2	R	.29 17.11
223-043	x 3/4	R	.32 18.99
223-058	10-24 x 1/2	R	.34 19.86
223-068	x 1"	PAN	.41 24.51
223-079	10-32 x 1/2	R	.34 19.86
223-086	x 3/4	R	.38 22.62
223-103	12-24 x 1/2	R	.39 23.35
223-120	1/4-20 x 1/2	R	.53 31.60
223-131	x 1"	H	.66 39.14
223-143	5/16-18 x 1/2	H	.77 45.52
223-152	x 1"	H	1.10 64.94