





## System PKZ 2 Motor Protectors Enclosures, Accessories

		For use with	Type	Price	
			Article No.		see price list
<b>Enclosures for Motor Protectors</b>					
	Insulating material Dust-tight NEMA Type 12	PKZ2/ZM-... +NHI + AGM + U or A + (R)H	<b>CI19EE-PKZ2-NA</b> 003183		NEMA Type 12 dust-tight industrial use enclosure with lift-off cover. Must be equipped with (R)H-PKZ2 door mounted handle. Comes with a 15 mm DIN rail, and provided with top and bottom steel plates and brass strip for continuity of ground.
	Steel General purpose NEMA Type 1	PKZ2/ZM-... +NHI + AGM + U or A or RE or RS	<b>CS3-PKZ2</b> 105073		General purpose enclosure with lift-off cover. Includes a rectangular cutout for the motor protector handle (not necessary to include the (R)H-PKZ2 door mounted handle). Also includes a knockout for the R(E)(S)-PKZ2 remote control drives and a knock-out for a pilot light.
<b>Enclosures for Motor Protector Combinations</b>					
	Insulating material Dust-tight NEMA Type 12 IEC Type IP 65	PKZ2/ZM-.../S + NHI(S) + AGM + U or A + (R)H-PKZ2	<b>CI43X-150-PKZ2-NA</b> 005352		Corrosion-resistant and dust-tight insulating material enclosure. Must be equipped with the (R)H-PKZ2 door mounted handle.
	Steel General purpose NEMA Type 1	PKZ2/ZM-.../S + NHI(S) + AGM + U or A + (R)H-PKZ2	<b>GKP23-PKZ2</b> 105370		General purpose enclosure with hinged cover. Must be equipped with the (R)H-PKZ2 door mounted handle.
	Steel Dust-tight NEMA Type 12		<b>GK23-PKZ2</b> 105253		
<b>Door/cover mounted handle NEMA/UL Type 3R, 12 and IEC IP 65</b>					
	Color: black for use as a main disconnect switch		<b>H-PKZ2</b> 043218		Door/cover interlock feature. Lockable in ON or OFF position. Up to three padlocks, hasp thickness 4 - 8 mm.
	For use in MCCs with PKZ2 turned 90°. Color: black for use as a main disconnect switch		<b>H-PKZ2-MCC</b> 201427		
	Color: red/yellow for use a main disconnect switch with Emergency-Stop function		<b>RH-PKZ2</b> 045591		Door cover interlocking feature. Lockable in the ON position only. Up to three padlocks, hasp thickness 4 - 8 mm.
	For use in MCCs with PKZ2 turned 90°. Color: red/yellow for use a main disconnect switch with Emergency-Stop function		<b>RH-PKZ2-MCC</b> 201428		
<b>Plug-in extension shaft for for/cover mounted handle</b>					
	can be extended as required for mounting depths from 171 to 300 mm		<b>A-H-PKZ2</b> 047964		