

DIL00M to DIL1AM Contactors Coil Voltages

AC	DIL00M (...)	DIL00M4 (...)	DIL00AM (...)	DIL0M (...)	DIL0AM (...)	DIL1M (...)	DIL1AM (...)
	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾
Standard voltages	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list
24V 50Hz	041764	000104	068921	009506	054590	049856	011886
48V 50Hz	048883	023834	045191	035609	080693	078332	040362
240V 50Hz	058375	095023	078413	002387	047471	045110	007140
500V 50Hz	065494	030953	038072	040355	085439	080705	042735
24V 60Hz	086851	099769	071294	011879	056963	052229	014259
115V 60Hz	079732	078412	090278	092560	035606	030872	094940
208V 60Hz	210224	210230	210218	210234	210232	210238	210236
600V 60Hz	210225	210231	210219	210235	210233	210239	210237
42V 50Hz, 48V 60Hz	060476	046933	061221	061253	061261	061269	061417
110V 50Hz, 120V 60Hz	060477	046926	061222	061254	061262	061270	061427
190V 50Hz, 220V 60Hz	060478	046927	061223	061255	061263	061271	061437
220V 50Hz, 240V 60Hz	061216	046928	061225	061256	061264	061272	061447
230V 50Hz, 240V 60Hz	061217	046929	061224	061257	061265	061273	061457
380V 50Hz, 440V 60Hz	061218	046930	061226	061258	061266	061274	043586
400V 50Hz, 440V 60Hz	061219	046931	061227	061259	061267	061275	043981
415V 50Hz, 480V 60Hz	061220	046932	061228	061260	061268	061375	044266
24V 50/60Hz	093970	097396	073667	007133	052217	047483	009513
42V 50/60Hz	088324	083288	088471	023744	068828	064094	026124
110V 50/60Hz	098716	073666	095024	085441	028487	023753	087821
230V 50/60Hz	043380	045969	043237	043665	043527	043695	043666
380V 50/60Hz	013289	007223	064175	016625	061709	056975	019005
Special voltages (i.e. voltages other than the standard voltages listed above) ²⁾	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list
...V 50Hz (12–600V)	939391	968920	999770	980695	923741	–	–
...V 50Hz (24–600V)	–	–	–	–	–	919007	983075
...V 60Hz (12–600V)	984478	971293	997397	983068	926114	–	–
...V 60Hz (24–600V)	–	–	–	–	–	921380	985448
DC	DIL00M-G(...)	DIL00M4-G(...)	DIL00AM-G(...)	DIL0M-G(...)	DIL0AM-G(...)	DIL1M-G(...)	DIL1AM-G(...)
	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾	Article No. ¹⁾
Standard voltages	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list
24V DC	048587	063171	048567	048597	048592	048605	048602
48V DC	048588	063172	048568	048598	048593	048606	048603
60V DC	048589	063173	048569	048599	048594	048607	063229
110V DC	048585	063169	048565	048595	048590	063230	048600
220V DC	048586	063170	048566	048596	048591	048604	048601
Special voltages (i.e. voltages other than the standard voltages listed above) ²⁾	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list	Price see price list
...V DC (12–250V)	915546	915232	915547	915551	915552	915553	915554

Notes:

- ¹⁾ To obtain the article number for ordering, read under selected type and coil voltage from the table above. Devices with **dual-voltage coils** must be ordered using **one** article number.
- ²⁾ When ordering special voltages, state the operating voltage selected from the range (...-...V) shown.