

ECX Enclosed Control

Table 1. Enclosed XT Non-Combo Starters, continued

Catalog Number	Description	List Price U.S. \$
ECX09D5BAA	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil	220.00
ECX09E5BAA	15 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil	245.00
ECX09F5BAA	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil	285.00
ECX09G5BAA	25 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil	340.00
ECX09H5BAA	32 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil	360.00
ECX09B5BBA	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	230.00
ECX09C5BBA	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	235.00
ECX09D5BBA	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	240.00
ECX09E5BBA	15 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	265.00
ECX09F5BBA	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	305.00
ECX09G5BBA	25 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	360.00
ECX09H5BBA	32 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP	380.00
ECX09B5BBA-A	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.1–0.16A	295.00
ECX09B5BBA-B	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.16–0.24A	295.00
ECX09B5BBA-C	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.24–0.4A	295.00
ECX09B5BBA-D	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.4–0.6A	295.00
ECX09B5BBA-E	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.6–1A	295.00
ECX09B5BBA-F	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 1–1.6A	295.00
ECX09B5BBA-G	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 1.6–2.4A	295.00
ECX09B5BBA-H	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 2.4–4A	295.00
ECX09B5BBA-I	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–6A	295.00
ECX09C5BBA-I	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–6A	300.00
ECX09C5BBA-J	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 6–10A	300.00
ECX09D5BBA-J	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 6–10A	305.00
ECX09D5BBA-K	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 9–12A	305.00
ECX09E5BBA-L	15 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 12–16A	330.00
ECX09F5BBA-L	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 10–16A	370.00
ECX09F5BBA-M	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 16–24A	370.00
ECX09G5BBA-M	25 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 16–24A	425.00
ECX09H5BBA-N	32 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 24–32A	445.00
ECX09B5BBA-R63/A	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 0.33–1.65A	395.00
ECX09B5BBA-R63/B	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 1–5A	395.00
ECX09B5BBA-R63/C	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–20A	395.00
ECX09C5BBA-R63/C	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–20A	400.00
ECX09D5BBA-R63/C	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–20A	405.00
ECX09E5BBA-R63/C	15 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 4–20A	430.00
ECX09F5BBA-R63/D	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 9–45A	470.00
ECX09G5BBA-R63/D	25 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 9–45A	525.00
ECX09H5BBA-R63/D	32 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, START/STOP, 9–45A	545.00
ECX09B5BHA	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	230.00
ECX09C5BHA	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	235.00
ECX09D5BHA	12 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	240.00
ECX09E5BHA	15 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	265.00
ECX09F5BHA	18 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	305.00
ECX09G5BHA	25 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	360.00
ECX09H5BHA	32 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA	380.00
ECX09B5BHA-A	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 0.1–0.16A	295.00
ECX09B5BHA-B	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 0.16–0.24A	295.00
ECX09B5BHA-C	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 0.24–0.4A	295.00
ECX09B5BHA-D	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 0.4–0.6A	295.00
ECX09B5BHA-E	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 0.6–1A	295.00
ECX09B5BHA-F	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 1–1.6A	295.00
ECX09B5BHA-G	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 1.6–2.4A	295.00
ECX09B5BHA-H	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 2.4–4A	295.00
ECX09B5BHA-I	7 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 4–6A	295.00
ECX09C5BHA-I	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 4–6A	300.00
ECX09C5BHA-J	9 amp, NEMA 1, 12, 13, 3R, 4X, 240 Vac coil, HOA, 6–10A	300.00