

New in the range

Circuit-breaker UL/CSA, IEC, thermomagnetic release, NZM...2...-NA

Rated current = rated uninterrupted current	Setting range overload release	Short-circuit release	Basic switching capacity 35 kA 240 V 60 Hz 25 kA 480 V 60 Hz 18 kA 600 V 60 Hz Part No.
---	-----------------------------------	--------------------------	--

$I_n = I_u$ A	I_r A	I_i A	
------------------	------------	------------	--

Terminal/box
terminal standard

System and line protection 3-pole, fixed overload release, terminal/box terminal standard, terminal

15	15	350	NZMB2-AF15-BT-NA
20	20	350	NZMB2-AF20-BT-NA
25	25	350	NZMB2-AF25-BT-NA
30	30	350	NZMB2-AF30-BT-NA
35	35	320-400	NZMB2-AF35-BT-NA
40	40	320-400	NZMB2-AF40-BT-NA
45	45	300-500	NZMB2-AF45-BT-NA
50	50	300-500	NZMB2-AF50-BT-NA
60	60	380-630	NZMB2-AF60-BT-NA
70	70	480-800	NZMB2-AF70-BT-NA
80	80	480-800	NZMB2-AF80-BT-NA
90	90	600-1000	NZMB2-AF90-BT-NA
100	100	600-1000	NZMB2-AF100-BT-NA
110	110	750-1250	NZMB2-AF110-BT-NA
125	125	750-1250	NZMB2-AF125-BT-NA
150	150	960-1600	NZMB2-AF150-BT-NA
175	175	1200-2000	NZMB2-AF175-BT-NA
200	200	1200-2000	NZMB2-AF200-BT-NA
225	225	1500-2500	NZMB2-AF225-BT-NA
250	250	1500-2500	NZMB2-AF250-BT-NA



Terminal/box
terminal standard

System and line protection 3-pole, adjustable overload release, terminal/box terminal standard,

20	15-20	350	NZMB2-A20-BT-NA
25	20-25	350	NZMB2-A25-BT-NA
32	25-32	350	NZMB2-A32-BT-NA
40	32-40	320-400	NZMB2-A40-BT-NA
50	40-50	300-500	NZMB2-A50-BT-NA
63	50-63	380-630	NZMB2-A63-BT-NA
80	63-80	480-800	NZMB2-A80-BT-NA
100	80-100	600-1000	NZMB2-A100-BT-NA
125	100-125	750-1250	NZMB2-A125-BT-NA
160	125-160	960-1600	NZMB2-A160-BT-NA
200	160-200	1200-2000	NZMB2-A200-BT-NA
250	200-250	1500-2500	NZMB2-A250-BT-NA

