

Plug-In Circuit Breakers for CPM/CPL

Type DNPL Duplex™, Independent Quadplex™, & Circuit Breaker Packs


Type DNPL ① ②

- ◆ 10,000 Amperes Interrupting Capacity at 120VAC, 120/240VAC, and 240VAC


Product Selection

Table 12. Duplex™ and Independent Trip Quadplex™ Plug-In Circuit Breakers


Duplex™		Quadplex™ Independent Trip			Quadplex™ Independent Trip				
Two Single Pole Circuits		Two Single Pole Circuits and One Double Pole Circuit			Two Double Pole Circuits				
10 per Shelf Carton		5 per Shelf Carton			5 per Shelf Carton				
120VAC		120VAC	120/240VAC	120VAC	120/240VAC				
		Ampere Rating			Ampere Rating				
Ampere Rating	Catalogue Number	Outer Left (1 Pole)	Centre (2 Poles)	Outer Right (1 Pole)	Catalogue Number	Outer Left & Right (2 Poles)	Centre (2 Poles)	Catalogue Number	Wire Size Range (Cu/AL 60°C or 75°C)
15-15	DNPL1515	15	15	15	DNPL151515	15	15	DNPL215215	#14 - 4 AWG
15-20	DNPL1520	15	20	15	DNPL152015	15	20	DNPL215220	#14 - 4 AWG
15-30	DNPL1530	15	25	15	DNPL152515	15	30	DNPL215230	#14 - 4 AWG
20-20	DNPL2020	15	30	15	DNPL153015	15	40	DNPL215240	#14 - 4 AWG
—	—	15	40	15	DNPL154015	20	20	DNPL220220	#14 - 4 AWG
—	—	15	50	15	DNPL155015	20	30	DNPL220230	#14 - 4 AWG



Requires One 1-Inch (25.4mm) Space



Independent Trip
Requires Two 1-Inch (25.4mm) Spaces



Independent Trip
Requires Two 1-Inch (25.4mm) Spaces

Type BP (Circuit Breaker Packs)

- ◆ Single carton packaged
- ◆ Represents common household combinations

Product Selection

Table 13. Plug-in Circuit Breaker House Paks

Contents	Catalogue Number	Contents	Catalogue Number
(3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP2	(16) BR115, (3) BR215, (1) BR230, (1) BR240	BP24
(10) BR115, (3) BR215, (1) BR230, (1) BR240	BP4	(14) BR115, (2) BR120, (1) BR230, (1) BR240	BP27
(2) DNPL1515, (1) DNPL215215, (1) DNPL152015, (1) DNPL153015, (1) DNPL154015	BP16	5 of DNPL1515, 1 of DNPL2020, 1 of DNPL153015, 1 of DNPL154015	BP31
(6) DNPL1515, (2) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP18	(1) BR120, (4) DNPL1515, (1) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP32
(1) DNPL1515, (3) DNPL151515, (2) DNPL153015, (1) DNPL154015	BP21	(10) BR115, (2) BR120, (1) BR215, (1) BR220, (1) BR230, (1) BR240	BP41
(3) DNPL1515, (3) DNPL151515, (1) DNPL153015, (1) DNPL154015	BP23	(3) DNPL1515, (1) DNPL153015, (1) DNPL154015, (1) DNPL2020, (1) DNPL1520	BP54



DNPL2020



DNPL155015



DNPL230230

① All Type DNPL Duplex™ and Quadplex™ circuit breakers carry listing for HACR applications.

② All 15 and 20 ampere single poles are switch-duty rated.