



Decorator standard grade receptacles

Product description

2-pole, 3-wire grounding
15A & 20A, 125V/AC



Design features

- Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant 
- Longer, wider strap provides 40% more contact area to wall board, virtually eliminating floating installations
- Patented built-in wire stripper for #14 and #12 AWG wire to speed installation
- Patented built-in wire looper for pre-looping
- High impact-resistant thermoplastic face and back body eliminates breakage
- Double-wipe ground contacts ensure long-term ground retention
- Easy access split circuit break-off tab
- Tri-combo screws accept Slotted-, Phillips, and Robertson-head tools for installation flexibility
- Terminal screws backed out and ready for wiring
- Side wire terminals accept up to #10 AWG solid wire
- Push-in terminals accept #14 AWG solid wire




TR1107-9



1107

Decorator tamper resistant duplex receptacles




Rating		Description	Color suffix	Catalog no.	
A	V/AC				
15	125	Tamper resistant NEMA 5-15R decorator duplex receptacle, side & push wire	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TR1107__	•
15	125	Auto grounding tamper resistant NEMA 5-15R decorator duplex receptacle, side & push wire	A, B, BK, LA, V, W	<input type="checkbox"/> TR1107-9__	•
20	125	NEMA 5-20 tamper resistant decorator duplex receptacle, side wire only	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TR1307__	•

cULus Listed to UL498, file no. E15058; NOM certified

Decorator duplex receptacles




Rating		Description	Color suffix	Catalog no.	
A	V/AC				
15	125	NEMA 5-15R decorator duplex receptacle, side & push wire	A, B, BK, GY, LA, V, W	<input type="checkbox"/> 1107__	•
15	125	Auto grounding NEMA 5-15R decorator duplex receptacle, side & push wire	A, BK, LA, V, W	<input type="checkbox"/> 1107-9__	•

Listed to UL498, file no. E15058; CSA certified to C22.2, no. 42; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White).



Dimensional information: B-68, B-69 **Specification information:** Please visit www.cooperwiringdevices.com
Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page F-21

 Tamper resistant