

## Modular connectivity points

### Modular jacks & adapters

#### Product description

Voice, data, Category 3 RJ11, Category 6 RJ45, Category 5E RJ45, RG6 F-Type coax

#### Design features

- 110 style modular jacks
- Data jacks have 8 positions and 8 conductors for high-speed LAN applications
- Category 3 jacks have 6 positions and 6 conductors for voice and/or data applications
- Category 6 jacks are rated for 650MHz, Category 5E jacks are rated for 160 MHz
- IDC termination for simple and fast installation
- Color coding wiring labels for both T568A/B and USOC
- Video connectors require no soldering
- All jacks and adapters clip smoothly into place in our flush-mount modular wallplates



5546-6



5547-5E



5547-3E



5552-5E



5550-5E

#### Modular jacks & adapters

Description	Features	Color suffix	Catalog no.
Data jack, category 6 RJ45	8-position, 8-conductor 568A/B wiring	LA, V, W	□ 5546-6__
Data jack, category 5e RJ45	8-position, 8-conductor 568A/B wiring	LA, V, W	□ 5547-5E__
Voice jack, category 3 RJ11	6-position, 6-conductor USDOC wiring	LA, V, W	□ 5547-3E__
Video connector, F-type coax	For RG6 applications TV/satellite	LA, V, W	□ 5552-5E__
Blank insert	For filling empty ports/solid blank face	LA, V, W	□ 5550-5E__

#### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: LA (Light Almond), V (Ivory), W (White).

LA	V	W
(Lt. Almond)	(Ivory)	(White)

**Specification information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)  
**Compliances, specifications and availability are subject to change without notice.**