

AAL06

DAL06P

SAL06P

Dimmers & lighting controls

All load dimmers

Product description


Single-pole & multi-location 600W/VA, 1000W/VA, 120V/AC

Rated for all common lighting loads - Dimmable LED, Dimmable CFL, INC/HAL, ELV, MLV, FLR

Design features • Rated for use w

- Rated for use with 300W of dimmable LED or CFL, and 600W of incandescent, magnetic low-voltage, electronic low-voltage and dimmable fluorescent
- Electro-mechanical push pad for ON/OFF operation with separate DIM/BRIGHT bar (AAL06)
- 10-second delayed OFF feature (AAL06)
- Selectable Rapid Start feature to ensure lamp start-up at low preset light levels (AAL06)
- LED light level display for presetting illumination levels and master/accessory units for multi-location control (AAL06)
- Adjustable low-end and high-end dimming range to prevent lamp flickering (AAL06)
- No de-rating required for CFL/LED in multi-gang installations (AAL06)

- Preset feature allows user to return to previous light level when turning lights ON (DAL06P, SAL06P, TAL06P)
- Adjustable low-end dimming range (DAL06P, SAL06P TAL06P)
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels (DAL06P, TAL06P)
- Fixed Rapid Start provides quick power burst to ensure lights start even at low preset light levels (SAL06P)
- No de-rating required in multi-gang installations (DAL06P, SAL06P, TAL06P)
- Each color kit package includes 3 colors (except SAL06P)
- Incandescent, magnetic low-voltage, CFL, LED, FLR, ELV offered in single unit on SAL06P




Rated for all common lighting loads Dimmable Compact Fluorescent (CFL) Dimmable Light-Emitting Diodes (LED) Electronic & Magnetic Low-Voltage (ELV) Incandescent/Halogen (INC/HAL)

All load dimmers

Rating					
W/AC	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Smart dimmer master, AL series, single-pole/multi-location with presets and LEDs, neutral required	C1, C2, C4, C5	□ AAL06
600	120	INC, HAL, FLR, MLV, ELV			
300	120	Dimmable LED/CFL	Decorator dimmer, AL series, single-pole/3-way, preset	C1, C2, C4, C5	□ DAL06P
600	120	INC, HAL, FLR, MLV, ELV			
300	120	Dimmable LED/CFL	Slide dimmer, AL series, - single-pole/3-way with preset & LED indicator	A, BK, GY, LA, V, W	□ SAL06P
600	120	INC, HAL, FLR, MLV, ELV			
300	120	Dimmable LED/CFL	Toggle dimmer, AL series, single-pole/3-way preset	C1, C2, C4, C5	□ TAL06P
600	120	INC, HAL, FLR, MLV, ELV			

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY).



Derating Information: F-19 **Dimensional Information:** A-47, A-48 **Specification Information:** Please visit www.cooperwiringdevices.com Mark 10* and AmbiStar* are registered trademarks of Philips Advance; Tu-Wire* is a registered trademark of Lutron. **Compliances, specifications and availability are subject to change without notice.**

TAL06P