

## Dimmers & lighting controls

### Decorator dimmers

#### Product description

Single-pole & 3-way

300W, 600W/VA, 1000W/VA, or 8A; 120V/AC or 277V/AC

Incandescent/halogen, magnetic low-voltage, electronic low-voltage, fluorescent, compact fluorescent, LED

#### Design features

- Preset feature allows user to return to previous light setting when turning lights on
- Integrated linear slide control for easy, precise operation
- All units are available in combined single-pole/3-way versions
- Device can be wired into either 3-way location (load side or line side)
- Neutral is not required for installation of device
- Replaces a standard switch and offers dimmer capabilities
- Square Law Dimming—perceived dimming level is proportional to the slider position
- Power failure memory
- Electrostatic discharge protection
- Precise color matching
- Compatible with any decorator wallplate



DF8AP



DF10P

#### Dimmers, back & side wire



Rating					
W/AC	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
1000	120	INC, HAL, MLV	Incandescent/halogen/magnetic low-voltage dimmer, single-pole/3-way with preset	A, B, BK, GY, LA, V, W	□ DF10P-__

cULus Listed to UL1472, file no. E47967; NOM certified

#### Fluorescent dimmers, back & side wire



Rating				
A	V/AC	Description	Color suffix	Catalog no.
8	120	Fluorescent dimmer; single-pole/3-way with preset; Mark 10®, AmbiStar® & Tu-Wire® compatible	A, B, BK, GY, LA, V, W	□ DF8AP-__
8	277	Fluorescent dimmer, single-pole/3-way with preset, Mark 10® compatible	A, B, BK, GY, LA, V, W	□ DF8AP7-__

cULus Listed to UL1472, file no. E47967; NOM certified

#### 0-10V Dimmer, back & side wire



Rating					
Watt	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
1200	120	Dimmable LED/FLR 0-10V ballasts	Decorator dimmer, single-pole/3-way, preset	C1, C2, C4, C5	□ DF10P-__
1600	277				
—	—	—	Color change faceplate for DF10P	A, BK, GY, LA, V, W	□ DCK1-__

cULus Listed to UL1472, file no. E47967; NOM certified

#### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY).

<b>A</b>	<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>V</b>	<b>W</b>					
(Almond)	(Brown)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)					
<b>A</b>	<b>W</b>	<b>V</b>	<b>LA</b>	<b>W</b>	<b>V</b>	<b>BK</b>	<b>W</b>	<b>V</b>	<b>BK</b>	<b>W</b>	<b>GY</b>
<b>C1 Color Kit</b>			<b>C2 Color Kit</b>			<b>C4 Color Kit</b>			<b>C5 Color Kit</b>		
A (Almond), W (White), V (Ivory)			LA (Light Almond), W (White), V (Ivory)			BK (Black), W (White), V (Ivory)			BK (Black), W (White), GY (Gray)		

**Derating Information:** F-19 **Dimensional Information:** A-46 **Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

Mark 10® and AmbiStar® are registered trademarks of Philips Advance; Tu-Wire® is a registered trademark of Lutron.

**Compliances, specifications and availability are subject to change without notice.**