Dimmers & lighting controls



Slide dimmers

Product description

Single-pole & 3-way 300W, 600W/VA, 1000W/VA, or 8A; 120V/AC or 277V/AC

Incandescent/halogen, magnetic low-voltage, electronic low-voltage, fluorescent, compact fluorescent, LED



- Preset feature allows user to return to previous light setting when turning lights ON
- · Integrated full slide control for easy, precise operation
- · Preset versions can be wired as single-pole or 3-way
- Device can be wired into either 3-way location (load side or line side)
- · Green LED softly illuminates when device is off, acting as a night light (preset versions only)

- · Neutral is not required for installation of device
- Replaces a standard switch and offers dimmer capabilities
- Square Law Dimming—perceived dimming level is proportional to the slider position
- · Power failure memory
- Electrostatic discharge protection
- · Precise color matching
- · Compatible with any decorator wallplate



SI061-V



SF10P

Dimmers, back & side wire

Dating





Ra					
w	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
600	120	Incandescent/halogen	Dimmer, single-pole non-preset	A, B, BK, GY, LA, V, W	☐ SI061
1000	120	Incandescent/halogen/ magnetic low-voltage	Dimmer, single-pole/3-way with preset & LED indicator	A, B, BK, GY, LA, V, W	□ SI10P

cULus Listed to UL1472, file no. E47967; NOM certified

Fluorescent dimmers, back & side wire





Α	V/AC	Description	Color suffix	Catalog no.
8	277	Fluorescent dimmer, single-pole/3-way with preset & LED indicator, Mark 10° compatible	A, B, BK, GY, LA, V, W	☐ SF8AP7

cULus Listed to UL1472, file no. E47967; NOM certified

0-10V Dimmer, back & side wire





naung					
Watt	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
1200	120	Dimmable LED/FLR 0-10V ballasts	Slide dimmer, single-pole/3-way, preset	A, B, BK, GY, LA, V, W	☐ SF10P
1600	277				

cULus Listed to UL1472, file no. E47967; NOM certified

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White).



Derating Information: F-19 Dimensional Information: A-46 Specification Information: Please visit www.cooperwiringdevices.com Compliances, specifications and availability are subject to change without notice.