


## Standard grade receptacles

### Product description

2-pole, 3-wire grounding  
2-pole, 2-wire non-grounding  
15A & 20A, 125V/AC



TR270





TWR270




270

### Design features

- Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant 
- Tamper and weather resistant receptacles provide both tamper resistant safety and ensure weather resistance in wet and damp outdoor locations 
- Longer, wider strap provides 40% more contact area to wall board, virtually eliminating floating installations
- Patented built-in wire stripper for #14 and #12 AWG wire to speed installation
- Push-in terminals accept #14 AWG solid wire
- Patented built-in wire looper for pre-looping
- High impact-resistant thermoplastic face and back body eliminates breakage
- Double-wipe ground contacts ensure long-term ground retention
- Easy access split circuit break-off tab
- Tri-combo screws accept Slotted-, Phillips-, and Robertson-head tools for installation flexibility
- Terminal screws backed out and ready for wiring
- Side wire terminals accept up to #10 AWG solid wire

### Tamper resistant duplex receptacles



Rating	A	V/AC	Description	Color suffix	Catalog no.	
15	125		Tamper resistant NEMA 5-15R duplex receptacle, side & push wire	A, B, BK, LA, V, W	□ TR270__	•
15	125		Auto grounding tamper resistant NEMA 5-15R, duplex receptacle, side & push wire	A, B, LA, V, W	□ TR270-9__	•
20	125		NEMA 5-20 tamper resistant duplex receptacle, 2-pole, 3-wire, side wire	A, B, BK, GY, LA, V, W	□ TR370__	

cULus Listed to UL498, file no. E15058; NOM certified

### Tamper & weather resistant duplex receptacles




Rating	A	V/AC	Description	Color suffix	Catalog no.	
15	125		Tamper & weather resistant NEMA 5-15R duplex receptacle, side & push wire	LA, V, W	□ TWR270__	•

cULus Listed to UL498, file no. E15058; NOM certified

### Duplex receptacles




Rating	A	V/AC	Description	Color suffix	Catalog no.	
15	125		NEMA 5-15R duplex receptacle, side & push wire	A, B, BLK, LA, V, W	□ 270__	•
15	125		Auto grounding NEMA 5-15R duplex receptacle, side & push wire	A, B, LA, V, W	□ 270-9__	•
15	125		NEMA 5-15R duplex receptacle, less ears, side & push wire	A, B, BK, LA, V, W	□ 4270__	•

Listed to UL498, file no. E15058; CSA certified to C22.2, no. 42; NOM certified

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White).



**Dimensional information:** B-68, B-69 **Specification information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)  
**Compliances, specifications and availability are subject to change without notice.**

 Indicates NAFTA compliant - Page F-21

 Tamper & weather resistant

 Tamper resistant