

C133ED / C133EDP 2.1MP HD MPX Fixed Dome Camera



C133EDPK4
2.1MP HD MPX Fixed Dome Camera 4 Pack



### **HD MPX Fixed Dome Cameras**

The FLIR 2.1MP HD Fixed Dome MPX camera uses the latest HDCVI technology to deliver excellent 1080p picture quality over coax cabling in any lighting condition. Ideal for retrofit applications, the camera is compatible with FLIR MPX DVRs offering an upgrade to HD resolution without the hassle of running new cables.

# **HD PICTURE QUALITY**

MPX 1080p HD picture quality over existing coax

• C133ED - 2.1MP HD, 1080p @ 25/30 FPS, 1/3" CMOS, 3.6mm lens, 70ft / 21m IR

### **EASY INSTALLATION**

Upgrade to HD without the expense of re-cabling

- BNC output MPX 1080p
- Wall / Ceiling mountable

# **SUPERIOR PERFORMANCE**

Virtually no latency, extended cable runs up to 2001ft / 610m

- IP66 weatherproof rated
- -22°F (-30°C) Cold Climate Capable



# **Specifications**


Camera	C133ED / C133EDP
Imaging Device	1/2.7" Exmor™
Effective Pixels	1920 (H) x 1080 (V)
Image Type	CMOS
Image Readout	Progressive Scan
Day/Night	Υ
Mechanical IR Cut Filter	Υ
Min. Illumination	0.1 Lux @ F1.2 (Color)
S/N Ratio	≥50dB (AGC OFF)
Horizontal Field of View	90°
IR Illumination Range	70ft / 21m; 12 IR LEDs
IR Wavelength	840~850nm
Video Output	Composite 1.0Vpp @ 75ohm
Electronic Shutter Range	1/60 (1/50) ~ 1/100,000 sec.
Optical	
Lens Type	Board Type
Focal Length	3.6mm
F-Number	2.0
Zoom	N
Iris Control Type / Adjustment	Electronic / Auto or Manual
Video	
Frame rates	25/30fps
Backlight Compensation	BLC/HLC
Wide Dynamic Range	True WDR
White Balance	Auto / ATW / Preset / Manual
Gain Control	AGC - 0-20 Selectable
Noise Reduction	2D/3D - Low/Mid/High Selectable
Window Blanking	Y - 15 Zone Selectable
Menu Languages	English, German, French, Spanish, Russian, Polish, Italian, Portuguese
Mechanical	
Construction	Aluminum Alloy
Product Dimensions (W x H)	3.7 x 3.1" / 94 x 79mm
Product Weight	0.7lbs / 0.3kg
Electrical	
Power Input	12V DC ±10%
Power Consumption	5W
Current Consumption	200mA MAX with IR LED
Environment	
Operating Temperature	−22° ~ 140°F / −30° ~ 60°C
Operating Humidity	≤85% RH
Ingress Protection	IP66
Vandal Resistance	N
Certifications	···
Certifications	FCC, CE, ROHS
	. 55, 52, 110110

#### **Ordering Information**

C133ED: 8-41430-01245-0 C133EDP: 8-41430-01299-3 C133EDPK4: 8-41430-01297-9


## **Package Dimensions**

C133ED / C133EDP: 5.4 x 5.4 x 4.5" / 137 x 137 x 114mm C133EDPK4: 11 x 4.6 x 11" / 279 x 117 x 279mm



## **Dimensions**





#### MARKHAM, ONTARIO

FLIR Systems, Inc. 250 Royal Crest Court Markham, ON L3R 3S1 Canada PH: +1 866.344.4674

## PORTLAND

Corporate Headquarters FLIR Systems, Inc. 27700 SW Parkway Ave. Wilsonville, OR 97070 USA PH: +1 866.477.3687

www.flir.com/security NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2015 FLIR Systems, Inc. All rights reserved. (Created 11/19/15)



 $<sup>^{\</sup>star}$  15FPS with WDR on