

1/C & 3/C, 5/8 kV, Non-Shielded Armored or Non-Armored Armorcast/Cold Shrink Splices

3M™ Three-Conductor Inline Splicing Kits TS Series

3M Three-Conductor Inline Splicing Kits TS Series are designed for nonshielded armored and non-armored solid dielectric cables rated up to 8 kV. Connectors are not included, order separately. See page 147 in the “Lugs

& Connectors” section for ordering information. **Meets requirements of IEEE 404.** Each kit makes one splice.



One-Conductor Unshielded, Stranded



Three-Conductor Unshielded, Stranded

3M™ Splice Kits TS-5/8 kV Series Selection (Stranded Conductor) Unshielded

1C Splice Kit	UPC (051141-)	3C Splice Kit	UPC (051141-)	Size AWG or kcmil
TS-5kVU-1C-8-4	045276	TS-5kVU-3C-8-4	045818	8-4
TS-5kVU-1C-3-300	045269	TS-5kVU-3C-3-300	045795	3-300
TS-5kVU-	045283	TS-5kVU-3C-350-1000*	045801	350-1000

*Cu only for 1000 Mem.

These products are only available in Canada.

1/C & 3/C, 5/8 kV, Shielded Armored or Non-Armored Armorcast/Cold Shrink Splices

3M™ Armored/Aarmorcast/Non-Armored Cable Splices TS Series

The 3M Three-Conductor Inline Splicing Kits TS-Series are designed for splicing shielded armored and non-armored cables, 5 kV and 8 kV. Connectors are not included, order separately. See page 147 in the “Lugs & Connectors” section for ordering information. **Meets requirements of IEEE 404.** Each kit makes one splice.



One-Conductor, Shielded, Stranded



Three-Conductor, Shielded, Stranded

3M™ Splice Kits TS-5/8 kV Series Selection (Stranded Conductor) Shielded

1C Splice Kit	UPC (051141-)	3C Splice Kit	UPC (051141-)	Size AWG or kcmil
TS-5kV-1C-6-3/0	045320	—	—	6-2
TS-5kV-1C-6-3/0	045320	TS-5kV-3C-2-3/0	04602	2-310
TS-5kV-1C-4/0-400	045375	TS-5kV-3C-4/0-500	04578	4/0-400
TS-5kV-1C-500-1000	045382	TS-5kV-3C-4/0-500*	—	500
TS-5kV-1C-500-1000	045382	TS-5kV-3C-600-750†	04612	750
TS-5kV-1C-500-1000	045382	—	—	2000

*Cu only.

† Resin Rejacketing.

These products are only available in Canada.