

Multi-Conductor Unshielded Cable

Low Voltage Thermostat CMR

Conductors:	Solid Bare Copper
Insulation:	PVC
Jacket:	PVC
Construction:	Conductors cabled
Temperature Rating:	60°C
Operating Voltage:	30 Volts
Applications:	Thermostat controls, door bells, security systems and other low voltage remote control systems where voltage does not exceed 30 volts.
Approvals:	NEC CMR or CSA CMG FT4



TEVELEC NUMBER	No. of Conds.	AWG Size	Stranding	Nominal Insulation	Nominal Jacket	Nominal O.D.	Weight Lbs/1000'
T2374	2	20	1	.010	.018	.150	11
T2375	3	20	1	.010	.018	.156	14
T2376	4	20	1	.010	.018	.161	18
T2377	5	20	1	.010	.018	.170	22
T2782	2	18	1	.010	.018	.168	16
T2783	3	18	1	.010	.018	.174	22
T2784	4	18	1	.010	.018	.180	28
T2785	5	18	1	.010	.018	.190	34
T2786	6	18	1	.010	.018	.205	39
T2788	8	18	1	.010	.018	.231	51
T2790	10	18	1	.010	.018	.254	63

Color Code Chart

Conductor	Color	Conductor	Color
1	Black	7	Blue
2	Red	8	Brown
3	White	9	Purple
4	Green	10	Gray
5	Orange	11	Pink
6	Yellow	12	Tan