

- **PRODUCTS**
- Hand Tools
- Holemaking
- Bending
- Fishing & Cable Pulling
- Wire & Cable Termination
- Voice Data Video
- Testing & Measurement
- Storage & Material Handling
- Hydraulic Pumps & Miscellaneous



**Name:**  
4-way 1 GHz Splitter

**Cat #:**  
VS1-4

**UPC #:**  
46243

**Spec:**

**Description:**

Bandwidth - 5 MHz to 1 GHz.

- Power Passive Port - designed to pass RF and DC power from one input to one output.
- Nickel-plated, zinc die-cast housing for excellent anti-corrosive protection.
- 100% solder-sealed tin packplate provides EMI/RFI shielding > -120dB
- Low insertion loss.
- Printed circuit board construction ensures consistent RF performance and excellent port-to-port isolation.
- Precision machine threaded "F" ports for perfect connector fit.
- F-Ports spaced at 1" on center to allow applicatoin of security sleeves and window filters.
- F-Ports comply with SCTE outdoor standards.

