USA Tel: 800.435.0786

Fax: 800.451.2632





- Highly visible green color rods can be easily threaded together and seen when working above ceilings, down walls, or under raised floors.
- 1/4" (6.4 mm) diameter fiberglass rods provide added rigidity when multiple sections are connected.
- 200 lbs. (0.9 kN) minimum pulling strength.
- Two different threaded tips accommodate various bundles of wire or cable.
- 540-24 includes one 3' (.91 m) Glo Stix[™] section for improved tip visibility.
- Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating. Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip.

	CAT. NO.	UPC NO.	DESCRIPTION
Ī	540-12	10504	Fish Stix 12' (3.6 m) kit with bullet nose and "J" hook threaded
			tips, packaged in clear plastic tube
	540-24	10506	Fish Stix 24' (7.3 m) kit with bullet nose and "J" hook threaded
			tips, packaged in clear plastic tube
	11426	11426	Whisk Nose Tip
	10497	10497	Replacement Hook Nose Tip
	10498	10498	Replacement Bullet Nose Tip
	11583	11583	Replacement 4' Fish Stix Section
	11584	11584	Replacement 6' Fish Stix Section
	11585	11585	Replacement 3' Glo Stix section
d	CDECIFICA	TIONE	

SPECIFICATIONS

Length	540-12: 12' (3.6 m) - (3) 4' (1.2 m) Fish Stix sections
	540-24: 24' (7.3 m) - (3) 6' (1.8 m) Fish Stix sections, (1) 3' (0.9 m) Fish
	Stix section, and (1) 3' Glo Stix section
Weight	540-12: 1.04 lbs. (0.5 kg)
	540-24: 1.94 lbs. (0.9 kg)
Material	540-12: 1/4" (6.4 mm) dia. fiberglass rod
	540-24: 1/4" (6.4 mm) dia. fiberglass rod

Glo Stix™



- Luminescent 3/16" fiberglass rods glow in the dark to make fishing voice, data and video wires easier in dark spaces, such as above ceilings, in walls, and below sub-floors.
- 3/16" (4.7 mm) diameter stix are more flexible for fishing in walls through an outlet box.
- Sturdy, steel-threaded connectors are interchangeable with Greenlee 1/4" (6.4 mm) Fish Stix.
- Clear, non-metalic storage tube keeps Glo Stix charged and ready to use.
- Kit includes (3) 5-foot (1.5 m) Glo Stix for a total of 15 feet (4.6 m), a bullet nose and a hook nose tip.
- 200 lbs. minimum pulling strength.
- Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating. Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip.

CAT. NO.	UPC NO.	DESCRIPTION
540-15	11422	Glo Stix 15' (4.6 m) Kit with bullet nose and "J" hook threaded tips, packaged in clear plastic tube
11426	11426	Whisk Nose Tip
10497	10497	Replacement Hook Nose Tip
10498	10498	Replacement Bullet Nose Tip
11427	11427	Replacement 5' (1.5 m) Glo Stix section

SPECIFICATIONS

Length	15' (4.6 m) – (3) 5' (1.5 m) sections
Material	3/16" (4.7 mm) dia. luminescent fiberglass rod