

# ELECTRIC & BATTERY-POWERED KNOCKOUT KITS

## LS50L Battery-Powered Knockout Punch Driver

Knockouts

**NEW**  
PRODUCT

AVAILABLE AS  
**BARE**  
TOOL



- Punch holes from any angle with the 360° rotating head.
- Punches up to 6" holes in 14 gauge mild steel and 2" holes in 14 gauge stainless steel.
- Slim, compact and lightweight design for reduced fatigue and easy control.
- Automatic retraction prevents damage to punch and die.
- One trigger controls all tool functions, no additional manual work required.
- Non-slip rubber grip for firm and comfortable hold.
- LED light illuminates dark work areas.

### SPECIFICATIONS

<b>Weight (driver with battery)</b>	5.05 lbs (2.29kg)
<b>Maximum Punch Force</b>	6 Tons (60kN)
<b>Charging Time</b>	22 min (RAL2/BL1380) or 15 min (RAL1/BL1815)
<b>Battery Voltage</b>	18V

CAT. NO.	UPC NO.	DESCRIPTION
LS50L11A	04951	Punching Tool Kit Includes: LS50L Battery Driver, (1) 18V Li-ion Battery, (1) 120V Battery Charger, (1) Spacer (1924AA), (1) 3/4-16 x 4 Drawstud (31872). (1) 3/8 x 4.8 Drawstud (209633)
LS50L11B	04956	Punching Tool Kit Includes: LS50L Battery Driver, (1) 18V Li-ion Battery, (1) 120V Battery Charger, (1) Spacer (1924AA), (1) 3/4-16 x 4 Drawstud (31872). (1) 3/8 x 4.8 Drawstud (209633), Slugbuster punches and dies for (1/2", 3/4", 1", 1-1/4", 1 1/2" and 2") conduit
<b>B</b> LS50LB	01131	LS50 punch driver and case only (no battery, charger, or accessories).



A PRODUCT VIDEO IS AVAILABLE. SCAN THIS QR CODE OR VISIT:  
[www.youtube.com/GreenleeDEMO](http://www.youtube.com/GreenleeDEMO)

## Battery-Powered Knockout Punch Driver Kits Parts List

	CAT NO.	UPC NO.	DESCRIPTION	HOLE SIZE				KIT CAT./UPC NO.	
				CONDUIT & PIPE SIZE	ACTUAL			LS50L11A LS60LA11 LS60LA120	LS50L11B LS60LB11 LS60LB120
					Ø INCH	Ø MM	Ø MM		
PUNCHES AND DIES	721-1/2	31756	1/2" Conduit Size Slug-Buster® Punch	1/2"	7/8	0.885	22.5		✓
	14722	14722	1/2" Conduit Size Die	1/2"	7/8	0.885	22.5		✓
	721-3/4	31757	3/4" Conduit Size Slug-Buster® Punch	3/4"	—	1.115	28.3		✓
	124AV	06972	3/4" Conduit Size Die	3/4"	—	1.115	28.3		✓
	721-1	31758	1" Conduit Size Slug-Buster® Punch	1"	—	1.362	34.6		✓
	126AV	04011	1" Conduit Size Die	1"	—	1.362	34.6		✓
	721-1-1/4	31759	1-1/4" Conduit Size Slug-Buster® Punch	1-1/4"	1-11/16	1.701	43.2		✓
	128AV	04013	1-1/4" Conduit Size Die	1-1/4"	1-11/16	1.701	43.2		✓
	721-1-1/2	31760	1-1/2" Conduit Size Slug-Buster® Punch	1-1/2"	1-15/16	1.951	49.6		✓
	440AV	04061	1-1/2" Conduit Size Die	1-1/2"	1-15/16	1.951	49.6		✓
DRAW STUDS AND MISC.	721-2	31761	2" Conduit Size Slug-Buster® Punch	2"	2-3/8	2.416	61.5		✓
	442AV	04063	2" Conduit Size Die	2"	2-3/8	2.416	61.5		✓
	1614SS	30043	Draw Stud - 3/8" x 2-13/16"					✓	✓
	31872	31872	Draw Stud - 3/4" x 4-1/8"					✓	✓
	1924AA	03248	Spacer Short					✓	✓
	33967	33967	Stud Adapter - 3/8"					✓	✓