

## 2011 PROFESSIONAL

### Circuit Seeker™ Microprocessor-Based Circuit Tracer

#### Easy circuit tracing, with no knobs or switches to set.

Our best circuit tracing system is expressly designed to save pros time. With its integrated Circuit Seeker microprocessor power, it requires minimal set up – and its transmitter automatically indicates open, live, or shorted line mode. Complete kit includes transmitter, receiver, and accessories in a handy carrying case.

2011/UPC No. 00521

#### Features

- Traces circuits in both metallic and nonmetallic conduit.
- Finds breaks in wires and shorts to ground.
- Incorporates auto gain circuitry for enhanced accuracy.
- Locates and identifies blown fuses.
- Supports transmitter-to-receiver distances up to 4 miles (6.5km) for closed circuit tracing.

#### Accessories included

Adapter lead	(2) 9V batteries
AC blades	Instruction video
Extension leads	Carrying case
Earphone/tube	

Easy-to-read displays for instant indications, plus clear audio indicators.

Case-cover-mounted operating information adds convenience.

Receiver auto off conserves batteries.

Rugged housings stand up to years of hard use.

Traces concealed wiring, locates junction boxes, and finds breakers for live or dead circuits – no need for power interruption.



#### Specifications

Capacity	0-600V AC/DC
Auto off	Transmitter, 30 min.; Receiver, selectable
Case size	14" x 12" x 4" (355mm x 305mm x 102mm)
Weight	3.56 lbs. (1615g)
Distance	3000 ft. to 4 mi. (varies with application)

## 2008 PROFESSIONAL

### Power Finder™ Open Circuit Tracer

#### Fast, simple, unenergized circuit tracing.

Also traces energized circuits in limited applications. Convenient and reliable, this complete circuit tracing kit is ready for years of professional duty.

2008/UPC No. 38786

#### Features

- Traces concealed wiring.
- Supports transmitter-to-receiver distances up to 4000 feet (1220m).

#### Accessories included

Transmitter plug
(2) Receptacle blades
Extension leads
(2) 9V batteries
Carrying case

Easy-to-read displays for instant indications, plus clear audio indicators.

Rugged housings stand up to years of hard use.

#### Specifications

Capacity	0-480V AC/DC
Case size	12" x 8-3/4" x 2" (305mm x 222mm x 51mm)
Weight	2.4 lbs. (1089g)
Distance	3000 ft.-4000 ft. (915m-1220m)