

555® CX/DX Series Electric Benders

NEW
PRODUCT

- The 555® Series, commonly referred to as the "triple-nickel", has been completely re-engineered with a rugged exterior for the most demanding environments.

SIMPLE. 2 SHOES CAN HANDLE 6 SIZES (1/2"-2") RIGID, EMT & IMC

ACCURATE. ABSOLUTE-ENCODER BASED CONTROL ON 555DX REDUCES SCRAP & REWORK

RELIABLE. MORE UPTIME TO BEND¹

¹ Solid-state electronics system rated for 1,000,000+ bends.



A PRODUCT VIDEO IS AVAILABLE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



SPECIFICATIONS

Capacity	1/2" - 2" Rigid / EMT / IMC / PVC Coated
Power Source	120 VAC, 20 amp GFCI
Weight	300 lbs.



CAT NO.	UPC NO.	DESCRIPTION
555CX	12425	Bender, Electric Conduit with Standard Pendant (120 VAC, 20A)
555CXE	13972	Electric Bender, with 13930 1/2" - 2" EMT Shoe Group (120 VAC, 20A)
555CXR	12426	Electric Bender, with 28007 1/2" - 2" Rigid Shoe Group (120 VAC, 20A)
555CXRE	12427	Electric Bender, with 12580 1/2" - 2" Rigid, EMT Group (120 VAC, 20A)
555DX	12428	Bender, Electric Conduit with Digital Angle Pendant (120 VAC, 20A)
555DXE	13973	Electric Bender, with 13930 1/2" - 2" EMT Shoe Group (120 VAC, 20A)
555DXR	12429	Electric Bender, with 28007 1/2" - 2" Rigid Shoe Group (120 VAC, 20A)
555DXRE	12430	Electric Bender, with 12580 1/2" - 2" Rigid, EMT Group (120 VAC, 20A)
555DX-22	49840	Electric Bender, with Digital Angle Pendant (220 VAC, 20A)
555DXR-22	49842	Electric Bender, with 28007 1/2" - 2" Rigid Shoe Group (220 VAC, 20A)
28007	28007	Shoe Group, 1/2" - 2" Rigid (555 Series)
13930	13930	Shoe Group, 1/2" - 2" EMT (555 Series)
12580	12580	Shoe Group, 1/2" - 2" Rigid/EMT Combination (555 Series)
12581	12581	Shoe Group, 1/2" - 2" PVC Coated Rigid (555 Series)
13856	13856	Roller Unit, 1-1/2" - 2" IMC (555 Series) Combination Shoe (use with 12580 shoe group)
12583	12583	Roller Unit, 1-1/2" - 2" EMT (555 Series) Single Groove Shoes (use with 23802 and 23816 shoe groups)
12584	12584	Roller Unit, 1-1/2" - 2" IMC (555 Series) Single Groove Shoes (use with 26330 shoe group)

CAT NO.	SHOE GROUP	555DX	555CX	555 CLASSIC
12580	Combination 1/2"- 2" EMT/Rigid ¹	✓	✓	
28007	1/2"- 2" Rigid	✓	✓	✓
13930	1/2"- 2" EMT	✓	✓	
23802	1/2"- 2" EMT	✓ ²	✓ ²	✓
26330	1-1/2"- 2" IMC	✓ ³	✓ ³	✓
12581	1/2"- 2" PVC Coated	✓	✓	
37279	1/2"- 2" PVC Coated	✓	✓	✓
12582	1/2"- 2" PVC Coated	✓ ⁴	✓ ⁴	
01700	1/2"- 2" PVC Coated	✓ ⁴	✓ ⁴	

¹ Can also bend 1/2" - 1-1/4" IMC, need optional 13856 squeeze roller assembly for 1-1/2" & 2" IMC bending.

² Need optional 12583 roller unit for 1-1/2" & 2" EMT bending on 555CX & 555DX models.

³ Need optional 12584 roller unit for 1-1/2" & 2" IMC bending on 555CX & 555DX models.

⁴ Need 00946 and 13861 support roller assemblies to bend 1/2" - 2" PVC coated rigid on 555CX & 555DX.

BENDING RADII COMBO SHOE GROUP

SHOE SIZE	INCHES	mm
1/2" EMT	4-5/16"	109.5
1/2" IMC/Rigid	4-1/4"	108.0
3/4" EMT	5-1/2"	139.7
3/4" IMC/Rigid	5-7/16"	138.1
1" EMT	7"	177.8
1" IMC/Rigid	6-15/16"	176.2
1-1/4" EMT	8-13/16"	223.8
1-1/4" IMC/Rigid	8-3/4"	222.3
1-1/2" EMT	8-3/8"	212.7
2" EMT	9-1/4"	235.0
2" IMC/Rigid	9"	228.6