



FISHTAPE, STEEL-240' (BULK PACK)

Steel Fish Tape - 240' x 1/8" (73.2 m x 3.2 mm) 3-PACK

Cat No: 52041744

UPC No: 783310100485

Description

- Oil-tempered spring steel for excellent fishing performance
- Dirt-free tape finish keeps hands cleaner during use
- Advanced comfort handle grip reduces fatigue
- Superior rapid tape pay-out and rewind
- Smaller Fish Eye with offset bend for improved fishing ability
- Improved low profile tip for easy fishing through all sizes of conduit
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly
- Rugged case design improves drop impact capability
- Flared case with Grip Ridges for no slip handling
- Available in 50 FT (15.2 m), 65 FT (19.8 m), 125 FT (38.1 m) and 240 FT (73.2 m) lengths
- 1/8 IN, 1/4 IN and flat steel profiles to accommodate different fishing situations

Specifications

- Accessory : R438B Swivel Ball Head for use on 1/8 IN Steel Fish Tapes, R438-BM Ball Tip Male Half, 439-1 12 IN (305 MM) Flexible Fish Tape Leader, 439-2 12 IN (305 MM) SPEED FLEX Leader (solder joints)
- Application : For Excellent Fishing Performance
- Length : 240.000 FT (73.200 M)
- Material : Steel
- Package : 3/PACK
- Replacement Part : RS438-240 Replacement Steel Tape - 240 FT (NO CASE), 10051 8-1/2 IN Case/Handle Replacement Kit, 10052 12 IN Case/Handle Replacement Kit
- Sub Brand : MagnumPRO
- Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength
- Weight : 8.500 LB (3.900 KG)
- Width : 1/8 IN (3.200 MM)