

# 30mm, IP 65, UL Type 4, PG 13.5 and 1/2" NPT

Plastic  
Limit switches

## Movement to be detected



## Operating head type

	Adjustable $\varnothing$ 3 stainless steel rod lever	Adjustable $\varnothing$ 3 fiber-glass rod lever	Spring rod	Flexible rod with insulated end
Conformity / $\ominus$ (N.C. contact with positive opening operation)				
Maximum actuation speed	m/s 1.5	m/s 1.5	m/s 1	m/s 1
Min. torque: - actuation	N.m 0.10	N.m 0.10	N.m 0.12	N.m 0.12
- positive opening operation	N.m -	N.m -	N.m -	N.m -

8

B11 = Snap action contacts	Catalog number	LS35P71B11	LS35P72B11	LS35P91B11	LS35P92B11
	Operation diagram				
D11 = Non-overlapping Slow action contacts	Catalog number	LS35P71D11	LS35P72D11	LS35P91D11	LS35P92D11
	Operation diagram				
C11 = Overlapping Slow action contacts	Catalog number	LS35P71C11	LS35P72C11	LS35P91C11	LS35P92C11
	Operation diagram				
L02 = Slow action contacts	Catalog number	LS35P71L02	LS35P72L02	LS35P91L02	LS35P92L02
	Operation diagram				
L20 = Slow action contacts	Catalog number	LS35P71L20	LS35P72L20	LS35P91L20	LS35P92L20
	Operation diagram				
B02 = Snap action contacts	Catalog number	LS35P71B02	LS35P72B02	LS35P91B02	LS35P92B02
	Operation diagram				
Weight (packing per unit)	oz.	3.52	3.52	2.82	2.82

## Approximate dimensions (mm)

