

# 30mm, IP66, UL Type 4X, PG 13.5 and 1/2" NPT

Metal  
Limit switches

Unidirectional	30° Cam Translation Movement				Multidirectional
<b>ø22 plastic roller lever on steel plunger</b>	<b>ø18 plastic roller lever</b>	<b>ø50 rubber roller lever</b>	<b>Adjustable ø18 plastic roller lever</b>	<b>Adjustable ø50 rubber roller lever</b>	<b>Spring rod lever</b>
1 m/s 7 N 24 N	EN 50047 (A shape) 1.5 m/s 0.1 N.m 0.32 N.m	1.5 m/s 0.1 N.m 0.32 N.m	1.5 m/s 0.1 N.m 0.32 N.m	1.5 m/s 0.1 N.m 0.32 N.m	1 m/s 0.12 N.m -
LS35M38B11	LS35M41B11	LS35M42B11	LS35M51B11	LS35M52B11	LS35M91B11
LS35M38D11	LS35M41D11	LS35M42D11	LS35M51D11	LS35M52D11	LS35M91D11
6.34	8.11	8.99	8.46	9.34	6.34

■ Closed contact / □ Open contact

