

**YAL30T12 : CANLUG-300KCML-
SHORT-1/2**



www.fci.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Length (Barrel)	Standard
Size (Wire)	300 kcmil
Stud Hole (Size)	1/2 in.
Stud Hole (Spacing)	One Hole
Tongue Angle	Straight
Tongue Width (in)	1.2 in.
Wire Type	Commercial Stranded Copper
Strip Length (in)	1-1/8 in.
Physical	
Element A Index	17
Approvals / Certifications	
UL Listed	No
CSA Certified	Yes
Other Features	
UPC	78181041721
Keyword	ya