

YAL252T38 : CANLG-1/0STR-
SHORT-3/8X1



www.fci.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Length (Barrel)	Standard
Size (Wire)	1/0 AWG
Stud Hole (Size)	3/8 in.
Stud Hole (Spacing)	1 in.
Tongue Angle	Straight
Tongue Width (in)	0.75 in.
Wire Type	Commercial Stranded Copper
Strip Length (in)	15/16 in.
Physical	
Element A Index	12
Approvals / Certifications	
UL Listed	No
CSA Certified	Yes
Other Features	
UPC	78181041692
Keyword	ya