

**YAL362N : CANLUG-600KCM-SHORT-  
NEMA**



[www.fci.com](http://www.fci.com)

**BURNDY® PRODUCTS**

**Specifications**

<b>Dimensional</b>	
Length (Barrel)	Standard
Size (Wire)	600 kcmil
Stud Hole (Size)	1/2 in.
Stud Hole (Spacing)	1-3/4 in.
Tongue Angle	Straight
Tongue Width (in)	1.73 in.
Wire Type	Commercial Stranded Copper
Strip Length (in)	1-3/4 in.
<b>Physical</b>	
Element A Index	22
<b>Approvals / Certifications</b>	
UL Listed	No
CSA Certified	Yes
<b>Other Features</b>	
UPC	78181041738
Keyword	ya