

YAL26T38 : CANLUG-2/0 STR-  
SHORT-3/8



*Experience. Technology. Answers.™*

www.burndy.com

**BURNDY® PRODUCTS**

**Specifications**

Dimensional	
Tongue Angle	Straight
Length (in)	1.91
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.73
Pad Width (in)	0.83
Other Features	
UPC	78181041699
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	2/0
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	13
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A -468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N