

YAL2CT38 : CANLUG-#2 STR-
SHORT-3/8



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Tongue Angle	Straight
Length (in)	1.78
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.11
B Length (in)	0.7
Pad Width (in)	0.61
Other Features	
UPC	78181041718
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	2
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Brown
Plated (Yes or No)	Y
Index Number	10
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N