

YAL6CT516 : CANLUG-#6 STR-  
SHORT-5/16



*Experience. Technology. Answers.™*

www.burndy.com

**BURNDY® PRODUCTS**

**Specifications**

Dimensional	
Tongue Angle	Straight
Length (in)	1.64
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.33
Barrel Type	Standard
Thickness	0.07
B Length (in)	0.75
Pad Width (in)	0.52
Other Features	
UPC	78181041760
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	6
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	5/16
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N