

YAL8CT14 : CANLUG-#8 STR-
SHORT-1/4



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Tongue Angle	Straight
Length (in)	1.19
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.07
B Length (in)	0.44
Pad Width (in)	0.47
Other Features	
UPC	78181041764
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	8
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Red
Plated (Yes or No)	Y
Index Number	6
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A -468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N