

YAL8CT516 : CANLUG-#8 STR-
SHORT-5/16



www.fci.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Length (Barrel)	Standard
Size (Wire)	8 AWG
Stud Hole (Size)	5/16 in.
Stud Hole (Spacing)	One Hole
Tongue Angle	Straight
Tongue Width (in)	0.47 in.
Wire Type	Commercial Stranded Copper Flexible Copper
Strip Length (in)	1/2 in.
Physical	
Element A Index	49
Approvals / Certifications	
UL Listed	No
CSA Certified	Yes
Other Features	
UPC	78181041766
Keyword	ya