

YAL6CT38 : CANLUG-#6 STR-
SHORT-3/8



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional

Tongue Angle	Straight
Length (Barrel)	Standard
Size (Wire)	6 AWG
Stud Hole (Size)	3/8 in.
Stud Hole (Spacing)	One Hole
Tongue Width (in)	0.63 in.
Wire Type	Commercial Stranded Copper
Strip Length (in)	7/16 in.

Other Features

UPC	78181041759
Category Path	Product type/Compression/Copper/Uninsulated/Terminal/Standard

Approvals / Certifications

CSA Certified	Yes
UL Listed	No Yes

Physical

Element A Index	7
-----------------	---