

YAL272T38 : CANLG-3/0STR-  
SHORT-3/8 X1



*Experience. Technology. Answers.™*

www.burndy.com

**BURNDY® PRODUCTS**

**Specifications**

**Dimensional**

Tongue Angle	Straight
Length (in)	2.84
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.13
B Length (in)	0.79
Pad Width (in)	0.91
E - in	1

**Other Features**

UPC	78181041702
-----	-------------

**General**

Number of Holes	2
-----------------	---

**Conductor(s)**

Copper Solid Size (Range)	3/0
Copper Stranded (Range)	3/0

**Physical**

Type of Plating	Tin - Electro Plated
Color Code	Orange
Plated (Yes or No)	Y
Index Number	14
Product Material	Copper

**Approvals / Certifications**

Industry Standards	UL468A -468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N