

F900 SKYBAY FIXTURE SERIES

"T8" 6 Lamp Instant Start High Bay Fluorescent Luminaire

Catalogue # F904-632-61IS-HB

Four Foot - 120 Volts
Instant Start Electronic Ballast
(89%Ballast Factor)



*Click on image to print
or save as PDF*



SPECIFICATIONS

- IES Procedures Tested 94%Efficient
- Total weight 15 lbs
- High output electronic ballast (89%BF)
- Up to 15,753 initial lumens
(with high lumen lamps)
- Total luminaire watts 174W

FEATURES

- Instant restart
- High (CRI) Color Rendering Index
- Economical re-lamping
- Lower fixture costs
- 92%white reflective surface
- Ideal for chain, pendant or surface
mounting ("V" hanging included)
- Anti-vibration cam-lock sockets
- Simple light level control
- High efficiency
- CSA/UL certified

FIXTURE OPTIONS

- Powder coated wire guard and/or
damage resistant clear or patterned
acrylic lens
- Stem-hanging bracket
- Available in color
(see JAFtech color chart)
- Multi level lighting control
- Occupancy and/or photo sensor
- Cord sets and plugs
- Available with 95% Total Reflectance
Silver Reflector
- Integrated emergency lighting

