



NUMERICAL READOUTS EVERY 1/8" (30-454 ONLY).

Stanley® Tape Rules

- 7" standout
- 1/2", 3/4" and 1" blade widths
- High-contrast blade for easy readability
- High-impact, high-visibility yellow case stands up to regular use
- Polymer coating extends the life of the blade
- Three-rivet, corrosion-resistant hook moves to allow accurate inside/outside measurements (1" blade only.)

Product SKU No.	Blade Length		Blade Width Inches	Box/Ctn
	Feet	Meters		
30-485	12	—	1/2	6 / 36
30-495	16	—	3/4	6 / 36
30-496 <i>cm Graduation</i>	16	5	3/4	6 / 36
30-455	25	—	1	6 / 24
30-454 <i>Fractional Read</i>	25	—	1	6 / 24
30-456 <i>cm Graduation</i>	26	8	1	6 / 24
30-464	30	—	1	6 / 24

FatMax® Closed Case Stainless Steel Long Tapes

- 3/8"-wide stainless steel blade designed to last
- 3-to-1 gear drive for fast rewinds
- High-impact ABS case withstands rugged conditions
- Rubber, slip-resistant grip assures solid hold
- Tru-Zero end hook allows accurate inside and outside measurements
- Steel roller cage protects case from being cut by blade during retraction

3 TO 1 GEAR DRIVE



Product SKU No.	Blade Length		Blade Width Inches	Box/Ctn
	Feet	Meters		
34-129	50	—	3/8	6 / 24
34-130	100	—	3/8	6 / 24

Stanley® Closed Case Steel Long Tapes

- 3/8" (10mm) wide yellow blade coated with polymer for enhanced durability
- High-impact, high-visibility yellow ABS case houses thick, steel blade with easy-to-read markings
- Easy-wind drum ensures streamlined usage
- End hook recoils neatly into contoured case



Product SKU No.	Blade Length		Blade Width Inches	Box/Ctn
	Feet	Meters		
34-103	50	—	3/8	6 / 24
34-106	100	—	3/8	6 / 24