

FatMax® Jab Saw

- SharpTooth™ Saw Technology cuts on push and pull strokes and is up to 50% faster than traditional tooth designs
- Sharpened tip punches through drywall with ease
- Hardened, tempered blade for cutting life
- Excellent for wood, plastic and drywall
- Slip-resistant handle is designed for strength and durability



| SKU # | BLADE LENGTH | | POINTS PER IN. | TEETH PER IN. | BOX QTY | CARTON QTY | UPC |
|--------|--------------|-----|----------------|---------------|---------|------------|--------------|
| | IN. | MM | | | | | |
| 20-556 | 6 | 152 | 9 | 8 | 6 | 36 | 076174205565 |

Cushion Grip Jab Saw

- Fully hardened, tempered blade is designed for long cutting life
- Sharp tip makes plunge cuts easy
- Teeth are engineered to cut fast and prevent clogging
- Ergonomically designed curved handle is cushioned for comfort



| SKU # | BLADE LENGTH | | POINTS PER IN. | TEETH PER IN. | BOX QTY | CARTON QTY | UPC |
|--------|--------------|-----|----------------|---------------|---------|------------|--------------|
| | IN. | MM | | | | | |
| 15-556 | 6 | 152 | 9 | 8 | 6 | 36 | 076174155563 |

Wood Handle Jab Saw

- Designed especially for making cuts in plasterboard
- Self-starting point sharpened for plunge cuts
- Blade is epoxy-bonded and ferruled to the handle for a connection that is three times as durable as non epoxy bonded blades



| SKU # | BLADE LENGTH | | POINTS PER IN. | TEETH PER IN. | BOX QTY | CARTON QTY | UPC |
|--------|--------------|-----|----------------|---------------|---------|------------|--------------|
| | IN. | MM | | | | | |
| 15-206 | 6 | 152 | 9 | 8 | — | 6 | 076174152067 |

SharpTooth™ Drywall Saw

- SharpTooth™ Saw Technology uses three cutting surfaces to cut 50% faster than conventional Stanley® Hand Saws
- Induction-hardened teeth hold up against abrasive drywall materials
- Hardwood handle for durability and comfort



| SKU # | BLADE LENGTH | | POINTS PER IN. | TEETH PER IN. | BOX QTY | CARTON QTY | UPC |
|--------|--------------|-----|----------------|---------------|---------|------------|--------------|
| | IN. | MM | | | | | |
| 15-025 | 15 | 381 | 9 | 8 | — | 2 | 076174150254 |