



16 OZ. JACKETED FIBERGLASS NAIL HAMMERS

Jacketed design provides superior overstrike protection for long life and safety. Cushion grip handle for added comfort. Rim-Tempered™ face reduces chipping. Fiberglass handle allows for maximum shock absorption. Bright yellow color makes it easy to locate.

Product ID No.	—Overall Length—		—Weight—		Box/Ctn
	in	mm	oz.	grams	
51-110 Curved Claw	13-1/4	335	16	450	6 / 6
51-518 Rip Claw	13-1/4	335	16	450	0 / 6



WOOD HANDLE FRAMING HAMMERS

Select straight grain, hickory handle. Triple wedge head-to-handle assembly prevents any loosening. Octagon contour handle for a controlled swing. High carbon, high polish steel head.

Product ID No.	—Overall Length—		—Weight—		Box/Ctn
	in	mm	oz.	grams	
51-356 Plain Face	16	406	20	570	2 / 12
51-357 Checkered Face	16	406	20	570	2 / 12
51-359 Plain Face	16	406	24	680	2 / 12
51-360 Checkered Face	16	406	24	680	2 / 12
51-362 Checkered Face	18	457	28	795	2 / 12



FIBERGLASS NAIL HAMMERS

High strength fiberglass handle core for durability. One-piece gray molded outer jacket to prevent fiberglass splintering. Contoured textured, ribbed vinyl grip minimizes slipping. Semi-polished high carbon 16 oz. head. Curve and rip claw available. Head fully heat treated with Rim Tempered™ face to reduce chipping.

Product ID No.	—Overall Length—		—Weight—		Box/Ctn
	in	mm	oz.	grams	
51-098 Curved Claw	13	330	16	450	6 / 6
51-099 Rip Claw	13	330	16	450	0 / 6



WOOD HANDLE NAIL HAMMERS

High-carbon, steel head. Fully heat treated and polished bell face. Hickory handle.

Product ID No.	—Overall Length—		—Weight—		Box/Ctn
	in	mm	oz.	grams	
51-613 Curved Claw	11-1/2	290	7	200	0 / 6
51-713 Curve Claw	13	330	13	370	0 / 6
51-616 Curved Claw	13-1/4	335	16	450	0 / 6
51-716 Rip Claw	13-1/4	335	16	450	6 / 6



WOOD HANDLE NAIL HAMMERS

Select straight grain, hickory handle. Triple wedge head-to-handle assembly prevents any loosening. Octagon contour handle for a controlled swing. High carbon, high polish steel head.

Product ID No.	—Overall Length—		—Weight—		Box/Ctn
	in	mm	oz.	grams	
51-350 Curved Claw	13	330	13	370	4 / 24
51-351 Curved Claw	13-1/4	337	16	450	4 / 24
51-352 Rip Claw	13-1/4	337	16	450	4 / 24
51-353 Curved Claw	13-1/4	337	20	570	4 / 24
51-354 Rip Claw	13-1/4	337	20	570	4 / 24
51-355 Long Handle Rip Claw	16	406	20	570	2 / 12



**WARNING: WEAR SAFETY GOGGLES
USER AND BYSTANDER.**

**FOR SAFETY AND PERFORMANCE
SELECT THE PROPER HAMMER**

NAIL HAMMERS: For common and finishing nail sets.
Not for masonry nails, cold chisels and other metal.