

Stanley® LED Tripod Flashlight – Standard

- Tripod design provides capability for hands-free use
- Magnetized and anodized aluminum tripod legs fold together to become a regular hand-held flashlight
- 3-6-9 technology gives user the choice to run the flashlight on 3, 6 or 9 AA batteries
- 100° rotational head with shatter-resistant lens focuses light where it's needed most
- One 1/2-watt bright white, long-lasting LED delivers a strong spot beam
- Slip-resistant rubber grip and feet
- On/Off switch
- Compliant with ANSI, CE and RoHs standards



SKU #	BATTERIES (NOT INCLUDED)	RUN TIME	BRIGHTNESS	BULB TYPE	BEAM DISTANCE		IMPACT RESISTANCE		HEIGHT		BOX QTY	CTN QTY	UPC
					FT.	M	FT.	M	IN.	MM			
95-112W	3, 6 or 9 AA	90 hrs (using 9 AA)	20 Lumens	1/2 W LED	282	86	3	0.9	11-8/9	302	—	6	076174951127

Stanley® LED Tripod Flashlight – Mini

- Tripod design provides capability for hands-free use
- Magnetized and anodized aluminum tripod legs fold to become a regular hand-held flashlight
- 100° rotational head with shatter-resistant lens focuses light where it's needed most
- Three 5mm bright white, long-lasting LEDs
- Slip-resistant rubber grip and feet
- On/Off switch
- Compliant with ANSI, CE and RoHs standards



SKU #	BATTERIES (NOT INCLUDED)	RUN TIME	BRIGHTNESS	BULB TYPE	IMPACT RESISTANCE		HEIGHT		BOX QTY	CTN QTY	UPC
					FT.	M	FT.	M			
95-111	3 AAA	10 hrs	8 Lumens	5mm LED	3	0.9	7-1/2	2.3	4	24	076174951110