

STANLEY® FATMAX XTREME® TAPE RULES

- 13' blade standout.
- 1-1/4" wide blade for easy readability.
- 150% larger hook* designed to grab on side, top or bottom for versatility.
- BladeArmor™ coating on the first 6" maximizes durability of the blade.
- High-visibility Mylar® polyester film extends life of entire blade and provides visibility in low lighting.
- Chrome case with durable rubber-holds up to heavy use.
- AirLock™ rubber slide lock is resistant to impact and makes locking and unlocking easy.
- Cushion grip provides comfortable, slip-resistant hold.
- Three-rivet, corrosion-resistant Tru-Zero™ end hook for accurate measurements.
- Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch.
- Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.

*Compared to Stanley(R) 1" tapes.



Product #	Blade Length	Blade Width	Stud Marking	Stud Marking
33-885	16 ft (5 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-890	25 ft (7.6 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-891L	8 m/26 ft cm graduation	1-1/4 in (31.7 mm)	16 in	19.2 in
33-895	30 ft (9.1 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-900	35 ft (10.7 m)	1-1/4 in (31.7 mm)	16 in	19.2 in

STANLEY® FATMAX® TAPE RULES

- 11' blade standout.
- 1-1/4" wide blade for easy readability.
- BladeArmor™ coating on the first 4-1/2" maximizes durability of the blade.
- Mylar® polyester film extends life of entire blade.
- High-impact ABS case with durable rubber-holds up to heavy use.
- Top-forward blade lock makes locking and unlocking easy.
- Cushion grip provides comfortable, slip-resistant hold.
- Three-rivet, corrosion-resistant Tru-Zero™ end hook for accurate measurements.
- Top edge: Major scale numbered in consecutive feet. Minor scale numbered in consecutive inches after each foot. Graduated in 16ths of an inch.
- Bottom edge: Numbered in consecutive inches. Graduated in 16ths of an inch.



Product #	Blade Length	Blade Width	Stud Marking	Stud Marking
33-716	16 ft (5 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-725	25 ft (7.6 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-726	8 m/26 ft cm graduation	1-1/4 in (31.7 mm)	16 in	19.2 in
33-730	30 ft (9.1 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-735	35 ft (10.7 m)	1-1/4 in (31.7 mm)	16 in	19.2 in
33-740	40 ft (12 m)	1-1/4 in (31.7 mm)	16 in	19.2 in

Mylar® is a registered trademark of DuPont Teijin Films.