

STANLEY® FATMAX XTREME® TORPEDO LEVEL



- Heavy-duty, die-cast aluminum body.
- Solid block vials provide accuracy of 0.0005 in/in (0.5mm/m).
- Machined leveling surface for improved accuracy.
- 180° rotating vial to duplicate angles.
- Magnified center vial for visibility.
- Rare-earth magnets for ultimate holding power.
- Pipe groove for use on rounded surfaces.



Product #	Type	Length	Vials	Hang Holes	Color
43-609	Magnetic	9-3/4 in (248 mm)	3 (1 Level, 1 Plumb, 1 180°)	2	Gunmetal

STANLEY® SHOCK-RESISTANT TORPEDO LEVELS MAGNETIC

- Heavy-duty aluminum frame and Bi-Material body with shock absorbing rubber ends for strength and durability.
- Vials provide accuracy of 0.002 in/in (2mm/m).
- Open, top-read vial provides maximum readability.
- Magnetic strip to allow for hands-free operation on metal surfaces.
- Lighted version with auto shutoff is designed for low-light locations.
- Pipe groove for use on rounded surfaces.



Product #	Type	Length	Vials	Hang Holes	Color
43-511	–	9 in (229 mm)	3 (1 Level, 1 Plumb, 1 45°)	2	Yellow/Black
43-512	Lighted	9 in (229 mm)	3 (1 Level, 1 Plumb, 1 45°)	2	Yellow/Black

STANLEY® CAST ALUMINUM TORPEDO LEVEL MAGNETIC

- Heavy-duty, cast aluminum frame.
- Vials provide accuracy of 0.002 in/in (2mm/m).
- Center top read vial for improved visibility.
- Magnetic strip to allow for hands free operation on metal surfaces.
- Pipe groove for use on rounded surfaces.



Product #	Length	Vials	Hang Holes	Color
42-465	9 in (229 mm)	3 (1 Level, 1 Plumb, 1 45°)	1	Silver/Yellow

