


Conduit Benders

Iron Conduit Benders

Additional Features:

- High strength steel handle features a swaged end for inserting conduit to correct overbends (Cat. Nos. 56203 & 56204 only).
- Bright orange color handle is easy to spot on the jobsite.



Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Weight (lbs.)
56208	conduit bender head	1/2" (13 mm)	-	2.1
56209	conduit bender head	3/4" (19 mm)	1/2" (13 mm)	3.2
56210	conduit bender head	1" (25 mm)	3/4" (19 mm)	5.5
56211	conduit bender head	1 1/4" (32 mm)	1" (25 mm)	16.6 NEW!
56203	assembled conduit bender w/#51427 handle	1/2" (13 mm)	-	5.5
56204	assembled conduit bender w/#51427 handle	3/4" (19 mm)	1/2" (13 mm)	6.6
56205	assembled conduit bender w/#51428 handle	1" (25 mm)	3/4" (19 mm)	11.6



Aluminum Conduit Benders

- Lightweight die-cast aluminum construction.
- The traditional Benfield® head design accurately and consistently performs common bends such as Stub Ups, Offsets, Back-to-Back and Saddle Bends.
- Bold cast-in benchmark symbols, degree scales and multiplier scales help save time on the job.
- Textured interior hook surface prevents conduit from rolling or twisting during bends.
- Wide foot pedal provides excellent stability and features angled grooves for extra traction.

Cat. No.	Description:	Thinwall/EMT	Rigid/IMC	Radius	Weight (lbs.)
56206	assembled aluminum conduit bender with #51427 handle	1/2" (13 mm)	-	4"	4.4
56207	assembled aluminum conduit bender with #51427 handle	3/4" (19 mm)	1/2" (13 mm)	5"	5.4



56206

Conduit Bender Handles

Bender Handles



51427

- Available in multiple sizes and lengths and are compatible with all Klein Tools conduit bender heads.
- High-strength steel eliminates flex and provides excellent feel, control and leverage.
- Handle features an enlarged diameter hollow end for inserting conduit to correct overbends (Cat. No. 51427).
- Bright orange color is easy to spot on the jobsite.

Cat. No.	Description:	Weight (lbs.)
51427	conduit bender handle - 38" L, 3/4" NPT tap size fits 1/2" and 3/4" bender heads and is replacement handle for #56206 and #56207.	3.5
51428	conduit bender handle - 44" L, 1" NPT tap size fits 1" bender head.	6.0
51429	conduit bender handle - 54" L, 1-1/4" NPT tap size fits 1-1/4" bender head.	8.9

All dimensions are in inches and (millimeters) unless otherwise specified.

WARNING: Always wear approved eye protection.

Armored Cable Cutter

BX and Armored Cable Cutter

- Cuts BX and 3/8" armored cable.
- Eliminates burrs.
- Does not nick cable.
- Easily cuts 3/8" flexible conduit and #10, 12, and 14 armored cables with up to 4 wires with a couple of turns of the handle.
- Depth of cut adjusts between standard MC and reduced diameter MC.
- Extra blade storage in handle.
- Use with Klein Tools replacement blade Cat. No. 53726 or 53726-SEN.

Cat. No.	Length	Weight (lbs.)
53725	7-1/4" (184 mm)	2.00

Replacement Parts

53726	BX cutter replacement blade	0.1
-------	-----------------------------	-----



53725

Conduit Scoring Tool

Electrician's Conduit Scoring Tool

- Durable zinc cast scoring tool eliminates spiraling
- Used for scoring 1/2", 3/4" and 1" EMT conduit.
- Klein-designed, patented scoring wheel scores and allows clean conduit snaps without leaving burrs inside.
- 1" scoring wheel conveniently located in base of the handle; no tools required to replace scoring wheels.
- Four roller tracks specifically designed for professional use.
- Compact, enclosed design for use on job sites.

Cat. No.	Length	Conduit Diameter	Weight (lbs.)
88906	6.02" (153 mm)	scores 1/2", 3/4" and 1" EMT conduit	1.25 NEW!

Replacement Parts

88907	1/2" and 3/4" EMT replacement scoring wheel	NEW!
88908	1" EMT replacement scoring wheel	NEW!



88906

88907

88908

NEW!

Carbide-Tipped Hole Cutters

Carbide Hole Cutter

Cat. No.	Size	Conduit & Pipe Sizes	Weight (lbs.)
31850	3/4"	-	.25 NEW!
31852	7/8"	1/2"	.30 NEW!
31854	1"	-	.35 NEW!
31856	1-1/8"	3/4"	.40 NEW!
31857	1-7/32"	-	.40 NEW!
31858	1-1/4"	-	.40 NEW!
31860	1-3/8"	1"	.45 NEW!
31862	1-7/16"	-	.40 NEW!
31864	1-1/2"	-	.45 NEW!
31866	1-3/4"	1-1/4"	.70 NEW!
31868	2"	1-1/2"	.80 NEW!
31870	2-1/2"	2"	.95 NEW!

Replacement Parts

31874	replacement hole cutter pilot bit	.05 NEW!
-------	-----------------------------------	-----------------



NEW!

31860

- Cuts quick, precise holes in stainless steel, mild steel, iron, copper and brass sheet up to 3/16" (5 mm) thick.
- Smooth start pilot drill bit for greater control.
- Split point pilot drill bit prevents bit walking.
- Integrated flange prevents the operator from drilling beyond the sheet metal.
- Ejection spring for easy slug removal.

All dimensions are in inches and (millimeters) unless otherwise specified.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to cut metallic pipes or cable wire.

WARNING: Never use on or near live electrical circuits.

WARNING: Do NOT cut cold PVC.