

## PVC-Cutters

### Ratcheting PVC-Cutter

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.

Cat. No.	PVC Cutting Capacity	Length	Weight (lbs.)
50500	1/2" – 1-1/4"	9" (229 mm)	1.10
<b>Replacement Parts</b>			
50503	50500 replacement blade		



50500

### Large Capacity Ratcheting PVC-Cutter

- Makes clean, burr-free cuts through PVC.
- High-leverage ratchet-action for maximum cutting power.
- Special heat-treated blades stay sharp longer and reduce pipe deformation.

Cat. No.	PVC Cutting Capacity	Length	Weight (lbs.)
50501	1/2" – 2"	16-1/2" (419 mm)	2.60
<b>Replacement Parts</b>			
50504	50501 replacement blade		



50501

### PVC Cutter

- Cuts up to 3/4" schedule 40 PVC.
- Makes clean burr-free cuts in PVC and flexible pipe.
- Reversible blade doubles life.
- Cuts 1-3/8" O.D. flexible plastic pipe.
- Steel construction for strength.
- Guide helps cut pipe squarely.
- Handle latch keeps tool closed.



50506



50549

Cat. No.	PVC Capacity	Flexible Pipe Capacity	Weight (lbs.)
50506	3/4" (19 mm) schedule 40	1-3/8" (35 mm)	1.00
<b>Replacement Parts</b>			
50549	50506 replacement blade		



All dimensions are in inches and (millimeters) unless otherwise specified.

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Never use on or near live electrical circuits.

**⚠WARNING:** Do NOT use to cut metallic pipes or cable wire.

**⚠WARNING:** Do NOT cut cold PVC.