KD-2x1CSK

2 Inputs to 1 Output HDMI Switcher, supports Ultra HD/4K

Key Features


- > Digital Switching: 2 HDMI Sources to 1 HDMI Display
- Resolution Support: SD, HD, and VESA up to UHD/4K (4096x2160/60/30/24 or 3840x2160/60/30/24)
- > Ultra HD/4K: Supports Ultra HD/4K Signal transmission
- > 3D Ready: Capability to pass 3D stereoscopic signal formats
- > Full Buffer[™] System: Manages TMDS re-clocking / signal re-generation, HDCP source & display authentication, Hot Plug Management and EDID Control handshake
- > EDID: Internal library with 16 default EDID configurations for each input, including native EDID data for any Output/Display
- > Lossless Compressed Digital Audio: Dolby[®] TrueHD, Dolby[®] Digital Plus and DTS-HD Master Audio[™]
- > Deep Color Support: Up to 12 bits/color (up to 8 bits/color@4K/60)
- > CEC: Fully Supported
- > I2C Communication: EDID and HDCP transparency from Display to Source
- > Licensing: Fully licensed and compatible with all HDMI and HDCP technologies
- > Control: Front panel push button and LEDs, Optical IR
- Major Control System Support: Compass Control[®], AMX[®], Control4[®], Crestron[®], KNX[®], RTI[®], Savant, URC[®], Honeywell[®], HAI[®], Leviton[®], etc.



Specifications

- » Inputs: 2 HDMI connectors
- » Outputs: 1 HDMI connector
- » TMDS bandwidth: 3.4 Gb/s
- » DDC Signal (Data): 5 Volts p-p (TTL)
- » HDMI Video/Audio Signal: 1.2 Volts p-p
- » HDMI Connector: Type A, 19 Pin Female
- » Mount: Shelf Mount
- » Accessories: Remote Control
- » Power Supply: KD-PS5V1A, 5V/1A, 100-240VAC, 50-60Hz, Interchangeable head
- » Product: 3.8" x 1.2" x 2.5", Weight: 0.4 lb.
- » Packaging: 6.3" x 4.2" x 3.35", Weight: 0.7 lbs.
- » Regulation: CE, RoHS, WEEE
- » Enclosure: Black Plastic

System Design Example





Ultra AK