

4K HDMI® Cables

Commercial HDMI Cables - CL3/FT4 UL Rated



HDMI Cables, support Ultra HD/4K, HDR, 3D, Ethernet, ARC

KD-HIF12X	12 ft. HDMI Cable	28 AWG	
KD-HIF16X	16 ft. HDMI Cable	28 AWG	
KD-HIF20X	20 ft. HDMI Cable	26 AWG	

Ultra HD
4K

HDR
HIGH DYNAMIC
RANGE

100 Mb/s
HDMI
ETHERNET CH.

3D
SUPPORT

AUDIO
RETURN
CHANNEL

1080P+
FULL HD
CERTIFIED

CL3/FT4
UL RATED

Key Features

- › **Ultra HD/4K Support:** 4096x2160 or 3840x2160 24/25/30Hz at 4:4:4 and 50/60Hz at 4:4:4
- › **HDR (High Dynamic Range):** More life-like images through a greater range of luminance levels
- › **Deep Color Support:** Up to UHD/4K 24/25/30Hz 4:4:4/12 bits or 50/60Hz 4:4:4/8 bit
- › **3D Support:** Capability to pass 3D stereoscopic signal formats
- › **Ethernet Channel:** 100 Mb/s Ethernet between two HDMI connecting devices
- › **Audio Return Channel:** Audio can be returned from display back to HDMI source for amplification and display

- › **Full HD 1080p+:** Guaranteed Performance
- › **Lossless Compressed Digital Audio:** Dolby® TrueHD, Dolby® Digital Plus, DTS-HD Master Audio™ and Dolby® Atmos
- › **OPEN EYE™ Technology:** Certified & tested for low loss and noise-free performance



LIMITED
10 YEAR
WARRANTY