

HiFi Commercial ProK HDMI Cables - CL3/FT4 UL Rated

Super Sonic Speed 31.5Gbps, 1080p, Ultra HD/4K, 3D, Ethernet, ARC with RedMere Technology

KD-HIFI30ProK	30 ft. HDMI Cable	26 AWG	Ultra HD/4K	
KD-HIFI40ProK	40 ft. HDMI Cable	26 AWG	Ultra HD/4K	
KD-HIFI50ProK	50 ft. HDMI Cable	24 AWG	Ultra HD/4K	
KD-HIFI60ProK	60 ft. HDMI Cable	24 AWG	Ultra HD/4K	
KD-HIFI75ProK	75 ft. HDMI Cable	24 AWG	Ultra HD/4K	



Key Features

- **31.5 Gbps Speed:** Super Sonic Bandwidth
- **RedMere® Technology:** Powers Ultra HD/4K resolution support
- **Ultra HD/4K:** 4K x 2k video resolution support for 4K-capable televisions and commercial applications such as Digital Movie Theaters, CAD, Post Production, Graphics and etc.
- **3D:** Capability to pass 3D stereoscopic signal formats
- **Ethernet Channel:** 100 Mb/s Ethernet between two HDMI connecting devices
- **Audio Return Channel:** Audio can be returned from display back to HDMI source for amplification and display

- **Full HD 1080p+:** Guaranteed Performance
- **OPEN EYE™ Technology:** Certified & tested for low loss and noise-free performance
- **Lossless Compressed Digital Audio:** Dolby® TrueHD, Dolby® Digital Plus and DTS-HD Master Audio™
- **Refresh Rates:** 120/240/480/600Hz
- **Deep Color:** 48 Bit

