

**Ground Plates**
T&B Catalog Number:

GP110

UPC Number:

78378680097

Status:

Active

Description:

Ground Plate Type GP - Copper Pole for Wire Range #2 Sol. - #8 Str.

Features

More efficient than butt-wrapping poles. Made of electrolytic sheet copper.

Built-in high-pressure connector for ground lead, or supplied with #6 AWG copper pigtail pre-attached. Plates are grooved for trapping moisture.

General

Style	Type GP - Copper Pole
Material	Copper
Wire Range	#2 Sol. - #8 Str.

Dimension Information

D (inches)	10
------------	----

Packaging

Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	56.8 lbs. per 100

Application Support

Overview	Available on Website
----------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com