


BELOW GROUND




ID SW DOUBLE BELL COUPLING

Size		Symbol	ØC	D	L	ØC	D	L
in	mm	No.	inches			millimeters		
2	53	40-2010	2.170	0.070	10.25	55.1	1.8	260.4
2½	63	40-2510	2.670	0.070	10.25	67.8	1.8	260.4
3	78	40-3010	3.170	0.070	10.25	80.5	1.8	260.4
3½	91	40-3510	3.670	0.070	10.25	93.2	1.8	260.4
4	103	40-4010	4.170	0.070	10.25	105.9	1.8	260.4
4½	116	40-4510	4.730	0.095	10.25	120.1	2.4	260.4
5	129	40-5010	5.230	0.095	10.25	132.8	2.4	260.4
6	155	40-6010	6.230	0.095	10.25	158.2	2.4	260.4



ID SW 5° DOUBLE BELL COUPLING

Size		Symbol	ØC	D	L	ØC	D	L
in	mm	No.	inches			millimeters		
2	53	40-2011	2.170	0.070	0.125	55.1	1.8	3.2
2½	63	40-2511	2.670	0.070	0.125	67.8	1.8	3.2
3	78	40-3011	3.170	0.070	0.125	80.5	1.8	3.2
3½	91	40-3511	3.670	0.070	0.125	93.2	1.8	3.2
4	103	40-4011	4.170	0.070	0.125	105.9	1.8	3.2
4½	116	40-4511	4.730	0.095	0.125	120.1	2.4	3.2
5	129	40-5011	5.230	0.095	0.125	132.8	2.4	3.2
6	155	40-6011	6.230	0.095	0.125	158.2	2.4	3.2



ID SW

ID SW SLEEVE

Size		Symbol	ØC	D	L	ØC	D	L
in	mm	No.	inches			millimeters		
2	53	40-2016	2.170	0.070	12	55.1	1.8	304.8
2½	63	40-2516	2.670	0.070	12	67.8	1.8	304.8
3	78	40-3016	3.170	0.070	12	80.5	1.8	304.8
3½	91	40-3516	3.670	0.070	12	93.2	1.8	304.8
4	103	40-4016	4.170	0.070	12	105.9	1.8	304.8
4½	116	40-4516	4.730	0.095	12	120.1	2.4	304.8
5	129	40-5016	5.230	0.095	12	132.8	2.4	304.8
6	155	40-6016	6.230	0.095	12	158.2	2.4	304.8

