# **CEILING FAN HEATER**

SGH SERIES

# <u>GET CAUGHT UP</u> IN ITS COMFORT!

This stylish ceiling fan heater will be the highlight of your garage! The SPIDER<sup>TM</sup> ceiling fan heater combines optimum performance, instant heat and a low noise level, all this in a distinctive design with a choice of striking colours.



#### NEW DESIGN: INCREASED AIR FLOW

A REINVENTION OF GARAGE HEATING INNOVATIVE AND UNIQUE DESIGN

DESIGNED SPECIFICALLY FOR RESIDENTIAL GARAGES

**CEILING INSTALLATION** FREEING UP FLOOR AND WALL SPACE

#### **CHOICE OF STRIKING COLOURS**



### IDEAL FOR:

#### GARAGE, WORKSHOP

#### COLOURS

standard: red, yellow

luxurious finish: stainless steel (see price list)

#### <u>FINISH</u>

polyester powdercoat or stainless steel

#### MANUFACTURING

- 22-gauge smooth steel housing
- quiet helicoidal fan
- thermal protection with automatic reset
- closed and permanently lubricated motor

#### ELEMENT

nichrome element producing instant heat


#### CONTROL

wall thermostat (not included) – the use of an electronic thermostat is strongly recommended

#### INSTALLATION

- ceiling surface mounted with bracket
- from adjacent walls at a minimum of: 12 in. (305 mm)
- from floor at a minimum of 8 ft. (2.4 m) and a maximum of 10 ft. (3 m)






## TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	COLOUR	HEAT RISE		WEIGHT		PRICE
CODE	WATTS	VOLTS		°C	°F	KG	LB	
SGH4002R	4000/3000	240/208	RED	46	83	4.5	10	317.00
SGH4002Y	4000/3000	240/208	YELLOW	46	83	4.5	10	317.00
SGH4002SS	4000/3000	240/208	STAINLESS STEEL	46	83	4.5	10	430.00

### TECHNICAL DRAWINGS



°STELPRO reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. Returns are not accepted for orders of products with optional colours. For all the latest models and updated prices, please refer to our web site at www.stelpro.com.