

# ARCHITECTURAL BASEBOARD

ALUMINUM - ALUX4 SERIES



## A HEATER WITH A LOT TO OFFER

The ALUX4 is an impressive blend of contemporary design and superior performance. Its durable steel cabinet is decorated with an elegant aluminum grille and offers a remarkable heat density of 500 W per linear foot. Its unique airflow configuration compliments its appearance making it the leader in its class and a popular choice for professionals in the industry.



**EXTRUDED ALUMINUM FRONT COVER WITH A UNIQUE AND LUXURIOUS DESIGN**

**EXTREMELY SOLID, IMPACT AND RUST RESISTANT**

**THREE WATT DENSITIES OFFERED**

**PERSONALIZED INSTALLATION**

BLANK SECTIONS, PEDESTALS AND CLEAN BACKS AVAILABLE

**NEW STYLISH WHITE SATIN FINISH**

### IDEAL FOR:

SHOPPING MALL, HOSPITAL, OFFICE, HOTEL, LOBBY, HALLWAY

### COLOURS

- standard: white, soft white
- luxurious finish: anodized aluminum (see price list)
- ORORA (optional): denim blue, midnight blue, turquoise, moss green, canary yellow, red, orange, anodized aluminum paint, gravel gray, charcoal, espresso, black (refer to [page 8 of the catalogue](#))

### FINISH

epoxy-polyester powdercoat or anodized aluminum finish

### MANUFACTURING

- dimensions: 4 3/8 in. x 6 3/4 in.
- solid 20-gauge steel cabinet and extremely resistant extruded aluminum front cover with a thickness equivalent to 10 gauge
- front air intake and top air discharge (bottom air intake available on demand [BT])
- thermal protection with automatic reset
- full-length wireway
- pencil-proof openings of less than 1/4 in. (6.4 mm) prevent foreign objects from entering the unit

### ELEMENTS

double tubular elements, stainless steel sheathed with boxed aluminum fins for improved heat dissipation; the elements are securely fastened at their centers, floating in nylon sleeves at each end, eliminating expansion and contraction noises

### CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in tamper-proof thermostat accessible without removing front grille, installed in the left or right junction box (optional)
- low voltage relay kit installed in the left or right junction box (optional)

### INSTALLATION

- surface mounted
- wall or floor mounted with or without pedestal kit (optional)
- at least 3 in. from the floor ([BT] models only)
- wiring compartments at both ends of unit
- for a continuous effect, custom blank sections with a simple attach system are available (optional)

## ACCESSORIES

PRODUCT	DESCRIPTION	PRICE
ALUX4T12*	built-in tamper-proof single pole thermostat	104.00
ALUX4T22*	built-in tamper-proof double pole thermostat	174.00
ALUX4RE153*	built-in electronic low voltage relay [15 A @ 120 V-347 V]	54.75
ALUX4RE156*	built-in electronic low voltage relay [6 A @ 600 V]	96.75
ALUX4RE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208-347 V]	74.25
ALUX4RM240T*	built-in mechanical low voltage relay c/w transformer 24 V [5000 W @ 208 V/6000 W @ 240 V]	73.25
ALUX4RM347T*	built-in mechanical low voltage relay c/w transformer 24 V [6000 W @ 347 V]	82.25
ALUX4RM347C*	electro. mecha. relay w/o transformer 24 V [6000 W @ 120-347 V]	60.75
ALUX4R841C1151*	built-in mechanical low voltage relay c/w transformer 24 V [6000 W @ 600 V]	119.00
ALUX4R841D1036*	built-in mechanical low voltage relay w/o transformer 24 V [6000 W @ 600 V]	105.00
PK6*	pedestal kit - single (kit of two)	110.00
PK6CAP	anodized aluminum (paint) pedestal kit - single (kit of two)	125.00
PK6D*	pedestal kit - double (kit of two)	200.00
PK6DCAP	anodized aluminum (paint) pedestal kit - double (kit of two)	200.00
ALUX4JS*	joiner strip (2 in. – 51 mm)	119.00
ALUX4JSCAP	anodized aluminum (paint) joiner strip (2 in. – 51 mm)	128.00
ALUX4IC90*	inside corner (back measures 8 3/4 in. – 222mm long on each side)	414.00
ALUX4IC90CA	anodized aluminum (finish) inside corner (back measures 8 3/4 in. – 222mm long on each side)	448.00
ALUX4OC90*	outside corner (back measures 8 3/4 in. – 222mm long on each side)	414.00
ALUX4OC90CA	anodized aluminum (finish) outside corner (back measures 8 3/4 in. – 222mm long on each side)	448.00
ALUX4CB**	clean back (fully finished, no mounting holes or knockouts)	179.00
ALUX4BT*	air inlet from below/output from top	---
ALUX4SA*	full width flush fit stand - height of 2 to 12 in – 51 mm to 305 mm	---
ALUX4SR*	full width recessed stand (19/32 in. – 15 mm) - height of 2 inches – 51 mm	---

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal

\* Add W for white or SW for soft white

\* Factory installed



# TECHNICAL SPECIFICATIONS

STANDARD DENSITY 500 W PER LINEAR FOOT		MEDIUM DENSITY 400 W PER LINEAR FOOT		LOW DENSITY 300 W PER LINEAR FOOT		VOLTAGE	LENGTH		WEIGHT		PRICE	
CODE	WATTS	CODE	WATTS	CODE	WATTS	VOLTS	MM	IN.	KG	LB	W OR SW	CA
ALUX406108	1000	ALUX406088	800	ALUX406068	600	208	600	23 5/8	4.1	9	412.00	457.00
ALUX406102	1000	ALUX406082	800	ALUX406062	600	240	600	23 5/8	4.1	9	412.00	457.00
ALUX406107	1000	ALUX406087	800	ALUX406067	600	277	600	23 5/8	4.1	9	412.00	457.00
ALUX406103	1000	---	800	---	600	347	600	23 5/8	4.1	9	412.00	457.00
---	1000	---	800	---	600	480	600	23 5/8	4.1	9	---	---
---	1000	---	800	---	600	600	600	23 5/8	4.1	9	---	---
ALUX409158	1500	ALUX409128	1200	ALUX409098	900	208	900	35 7/16	5.9	13	471.00	516.00
ALUX409152	1500	ALUX409122	1200	ALUX409092	900	240	900	35 7/16	5.9	13	471.00	516.00
ALUX409157	1500	ALUX409127	1200	ALUX409097	900	277	900	35 7/16	5.9	13	471.00	516.00
ALUX409153	1500	ALUX409123	1200	ALUX409093	900	347	900	35 7/16	5.9	13	471.00	516.00
ALUX409155	1500	---	1200	---	900	480	900	35 7/16	5.9	13	471.00	516.00
ALUX409156	1500	---	1200	---	900	600	900	35 7/16	5.9	13	471.00	516.00
ALUX412208	2000	ALUX412168	1600	ALUX412128	1200	208	1200	47 1/4	7.7	17	532.00	577.00
ALUX412202	2000	ALUX412162	1600	ALUX412122	1200	240	1200	47 1/4	7.7	17	532.00	577.00
ALUX412207	2000	ALUX412167	1600	ALUX412127	1200	277	1200	47 1/4	7.7	17	532.00	577.00
ALUX412203	2000	ALUX412163	1600	ALUX412123	1200	347	1200	47 1/4	7.7	17	532.00	577.00
ALUX412205	2000	ALUX412165	1600	---	1200	480	1200	47 1/4	7.7	17	532.00	577.00
ALUX412206	2000	ALUX412166	1600	---	1200	600	1200	47 1/4	7.7	17	532.00	577.00
ALUX415258	2500	ALUX415208	2000	ALUX415158	1500	208	1500	59 1/16	9.1	20	592.00	637.00
ALUX415252	2500	ALUX415202	2000	ALUX415152	1500	240	1500	59 1/16	9.1	20	592.00	637.00
ALUX415257	2500	ALUX415207	2000	ALUX415157	1500	277	1500	59 1/16	9.1	20	592.00	637.00
ALUX415253	2500	ALUX415203	2000	ALUX415153	1500	347	1500	59 1/16	9.1	20	592.00	637.00
ALUX415255	2500	ALUX415205	2000	ALUX415155	1500	480	1500	59 1/16	9.1	20	592.00	637.00
ALUX415256	2500	ALUX415206	2000	ALUX415156	1500	600	1500	59 1/16	9.1	20	592.00	637.00
ALUX418308	3000	ALUX418248	2400	ALUX418188	1800	208	1800	70 7/8	11.3	25	651.00	696.00
ALUX418302	3000	ALUX418242	2400	ALUX418182	1800	240	1800	70 7/8	11.3	25	651.00	696.00
ALUX418307	3000	ALUX418247	2400	ALUX418187	1800	277	1800	70 7/8	11.3	25	651.00	696.00
ALUX418303	3000	ALUX418243	2400	ALUX418183	1800	347	1800	70 7/8	11.3	25	651.00	696.00
ALUX418305	3000	ALUX418245	2400	ALUX418185	1800	480	1800	70 7/8	11.3	25	651.00	696.00
ALUX418306	3000	ALUX418246	2400	ALUX418186	1800	600	1800	70 7/8	11.3	25	651.00	696.00
ALUX421358	3500	ALUX421288	2800	ALUX421218	2100	208	2100	82 11/16	13.2	29	712.00	757.00
ALUX421352	3500	ALUX421282	2800	ALUX421212	2100	240	2100	82 11/16	13.2	29	712.00	757.00
ALUX421357	3500	ALUX421287	2800	ALUX421217	2100	277	2100	82 11/16	13.2	29	712.00	757.00
ALUX421353	3500	ALUX421283	2800	ALUX421213	2100	347	2100	82 11/16	13.2	29	712.00	757.00
ALUX421355	3500	ALUX421285	2800	ALUX421215	2100	480	2100	82 11/16	13.2	29	712.00	757.00
ALUX421356	3500	ALUX421286	2800	ALUX421216	2100	600	2100	82 11/16	13.2	29	712.00	757.00
ALUX424408	4000	ALUX424328	3200	ALUX424248	2400	208	2400	94 1/2	15.4	34	772.00	817.00
ALUX424402	4000	ALUX424322	3200	ALUX424242	2400	240	2400	94 1/2	15.4	34	772.00	817.00
ALUX424407	4000	ALUX424327	3200	ALUX424247	2400	277	2400	94 1/2	15.4	34	772.00	817.00
ALUX424403	4000	ALUX424323	3200	ALUX424243	2400	347	2400	94 1/2	15.4	34	772.00	817.00
ALUX424405	4000	ALUX424325	3200	ALUX424245	2400	480	2400	94 1/2	15.4	34	772.00	817.00
ALUX424406	4000	ALUX424326	3200	ALUX424246	2400	600	2400	94 1/2	15.4	34	772.00	817.00

Add W for white, SW for silica white or CA for clear anodized (finish) (consult the optional colours chart or contact your °STELPRO representative for all other colours)  
 --- not available

## TECHNICAL DRAWINGS

