



BURNDY Catalog Number
UPC Number
Description
Status

YBA38FX
 7818104636977
 500FX-NEMA W/BRKAWY SLOT
 Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	6.76
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.27
B Length (in)	2.81
Pad Width (in)	1.62
E - in	1.75
Strip Length	2-7/8
General	
Number of Holes	2
Product Description	Cu&Al Compression Terminals, 2 Holes/W/O/insp W, 535.3 Flex(1325/24) 500 kcmil nom, 600V-35kV, 1/2" (12)stud, 1" to 1.75" spacing, Tin plated, Pink, L99 Index
Conductor(s)	
Flex (Class G) Size - Range	500 kcmil
Flex (Class H) Size - Range	500 kcmil
Flex (Class I) Size - Range	500 kcmil
Copper Solid Size (Range)	N/A
DLO Size (Range)	535.3 (1325/#24)
Copper Stranded (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Pink
Plated (Yes or No)	Y
Index Number	L99
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175